

Item #	Part	Model	Spec	Relay Description	Relay poles	Relay volt	Amp rating	Relay coil	Contact Type	Relay config	Circuit Protect.
1	31075502	MR-TAXS	6932	MR-TAXS, part #31075502, Spec 6932, 1-pole, 240V, relay with 180V-240V control coil, 3-prewired leads, mercury contacts, in a submersible enclosure.	1	240	100	240	Mercury	N.O.	None
2	31075500	MR-TD	6245	MR-TD, Spec 6245, 31075500; 1-pole, 120V, Norm Open; Form A mercury contact, 30A; Load protection: Fuse; Coil voltage: 120V; Control circuit source: Line; Control circuit arrester: Spark Gap; in a weather proof case.	1	120	30	120	Mercury	N.O.	Fuse
3	33132200	MTR-KD	6790	MTR-KD, Spec 6790, 33132200; 1-pole, 120V, Norm Open; Form A mercury contact, 60A; Load protection: Fuse; Coil voltage: 120V; Control circuit source: Line; Control circuit arrester: Spark Gap; in a weather proof case.	1	120	60	120	Mercury	N.O.	Fuse
4	33132600	MTR-KG	6794	MTR-KG, Spec 6794, 33132600; 1-pole, 120V, Norm Open; Form A mercury contact, 60A; Load protection: Fuse; Coil voltage: 120V; Control circuit source: Line; Photocell provision: Mounted Receptacle; Control circuit arrester: Spark Gap; in a weather proof case.	1	120	60	120	Mercury	N.O.	Fuse
5	33184000	MTRR-KD	6859	MTRR-KD, Spec 6859, 33184000; 1-pole, 120/240V, Norm Closed; Form B mercury contact, 60A; Load protection: Fuse; Coil voltage: 120V; Control circuit source: Line; Control circuit arrester: Spark Gap; in a weather proof case.	1	120	60	120	Mercury	N.C.	Fuse
6	33132000	MTR-XD	6788	MTR-XD, Spec 6788, 33132000; 1-pole, 120V, Norm Open; Form A mercury contact, 30A; Load protection: Fuse; Coil voltage: 120V; Control circuit source: Line; Control circuit arrester: Spark Gap; in a weather proof case.	1	120	30	120	Mercury	N.O.	Fuse
7	33132400	MTR-XG	6792	MTR-XG, Spec 6792, 33132400; 1-pole, 120V, Norm Open; Form A mercury contact, 30A; Load protection: Fuse; Coil voltage: 120V; Control circuit source: Line; Photocell provision: Mounted Receptacle; Control circuit arrester: Spark Gap; in a weather proof case.	1	120	30	120	Mercury	N.O.	Fuse
8	33063800	MTR-11-56-480	None	MTR-11-56-480, 33063800; 2-pole, 480V, Norm Open; Form A mercury contact, 100A; internal transformer control source with 120V coil; Load protection Fuse; load and control circuit arresters.	2	480V	100	120	Mercury	N.O.	Fuse
9	33079200	MTR-21-54-480	none	MTR-21-54-480, 33079200; 2-pole, 480V, Norm Open; Form A mercury contact, 100A; internal transformer control source with 120V coil; Load protection Fuse; HOA & panel board arresters.	2	240/480	100	120	Mercury	N.O.	Fuse