

Home Entertainment

Innovation and Convenience from Hubbell



Make your home theater the envy of the neighborhood with flexible multimedia and wire management. This future-ready technology upgrades your home.



RECESSED RECEPTACLES

Install furniture and panel displays flush against the wall. Recessed boxes install easily on studs, no extra hardware needed.



FLAT TV CONNECTION ENCLOSURES

Combine HDMI connections and surge protection in one assembly that enables optimal performance. It fits flush to the wall with no dangling cords.



NETWORK ENCLOSURES

Dependable and flexible management of your multimedia entertainment system.



FLOOR BOX

Easy access to power and data that doesn't sacrifice your home's style.



SURGE PROTECTED OUTLET

Protect computers and expensive electronics. Install surge protected power outlets.

Home Entertainment

Innovation and Convenience from Hubbell



netSELECT® Non-Metallic Network Enclosures

Description		Dimensions: Inches (mm)			Module Unit Capacity	Catalog Number
		Height	Width	Depth		
14-inch network enclosure	With hinged vented door	16.2" (412)	17.5" (445)	4.35" (111)	5	NSOBXP14
	14" height box only	13.5" (343)	17.1" (434)	3.95" (100)	5	NSOBXP14B
	Hinged vented door	16.2" (412)	17.5" (445)	0.4" (10)	-	NSOBXP14D
28-inch network enclosure	With hinged vented door	30" (762)	17.5" (445)	4.35" (111)	11	NSOBXP28
	28" height box only	27.7" (704)	17.1" (434)	3.95" (100)	11	NSOBXP28B
	Hinged vented door	30" (762)	17.5" (445)	0.4" (10)	-	NSOBXP28D
42-inch network enclosure	With hinged vented door (2-piece)	45.1" (1146)	17.5" (445)	4.35" (111)	16	NSOBXP42
	42" height box only	42.6" (1082)	17.1" (434)	3.95" (100)	16	NSOBXP42B
	Hinged vented door (2-piece)	45.1" (1146)	17.5" (445)	0.4" (10)	-	NSOBXP42D



FPTV Connection Enclosures

Description	Catalog Number
2-gang in-wall enclosure, white, 8.16" x 7.92" x 3.37"	NSAV62M
4-gang in-wall enclosure, white, 14.80" x 7.92" x 3.37"	NSAV124M
New work stud brackets	NSAV6NW

Accessories

Power kit		HDMI frame		Snap fit connectors			
Surge protected	Tamper-resistant	1-port	2-port	HDMI	F-connector	Cat 5e jack	Cat 6 jack
NSOKPS	NSOKPTR	NS801W	NS802W	SFHC14W	NSF70W	NSJ5EW	NSJ6W

Tamper-Resistant Recessed Receptacles, 2 Pole/3 Wire

Description		Color	Catalog Number
Single gang		Ivory	RR1510I
		Light Almond	RR1510LA
		White	RR1510W
Recessed duplex receptacle, 15A 125V, NEMA 5-15R, 2 pole/3 wire, grounding, side wire terminations	2-gang with feedthrough	Ivory	RR1512I
		Light Almond	RR1512LA
		White	RR1512W
2-gang with snap fit		Ivory	RR1514I
		Light Almond	RR1514LA
		White	RR1514W
Clock hanger, 15A 125V, NEMA 5-15R, 2 pole/3 wire, grounding, back and side wire terminations		Ivory	RR151CHITR
		White	RR151CHWTR



Make your homebuyer options stand out!
Hubbell products enhance your home tech offerings.



IDEVICES
INSTINCT

Wall switch features built-in Alexa and motion sensors



IDEVICES
WALL SWITCH

Works with HomeKit, Alexa, Google Assistant and Alarm.com



IDEVICES
WALL OUTLET

Provides individual receptacle control and energy monitoring



IDEVICES
ZWAVE DIMMER

Works with most security platforms and Z-Wave hubs