


Category 6 UTP System with *COBRA-LOCK*[™] Termination Technology



COBRA-LOCK[™] TERMINATION IS

- **FAST:** All four pairs terminated at once by hand
- **RELIABLE:** Designed to support Cat 6, termination is held in constant compression
- **EFFICIENT:** Terminate more jacks per hour


Termination Process



STEP 1:

Lace wires into wire manager, then trim flush

Wire manager securely retains wires for either A or B wiring and is keyed to ensure correct polarity to jack body.



STEP 2:

Insert wire manager and engage COBRA-LOCK

Jack body terminates all wires at once and actively retains termination integrity.



STEP 3:

Easily Re-Terminate

Release COBRA-LOCK[™] with a small screwdriver; wire manager can be reused up to 25 times.

Category 6 Jack Specifications



- Exceeds TIA 568.2-D component requirements
- Short links (less than 10M) supported
- Designed and tested for 1.5A of continuous current per pair

Category 6 Jack Standards

- TIA-568 Category 6 component
- IEC 60603 Category 6 compliant
- Qualified to 150% of IEEE 802.3bt current level
- IEC60512-99-002 for de-matting endurance under PoE load
- UL Plenum rated



NEXTSPEED® Category 6 Jacks with COBRA-LOCK™ Termination

Color	Single Pack
Black	HJU6BK
Blue	HJU6B
Gray	HJU6GY
White	HJU6W

Add 24 to Catalog Number for 24-pack

Additional colors: **BN** (Brown), **GL** (Gold), **GN** (Green), **EI** (Ivory), **OW** (Office White), **OR** (Orange), **PK** (Pink), **P** (Purple), **R** (Red), **Y** (Yellow)



NEXTSPEED® COBRA-LOCK™ Field Termination Plug

Category 6 **SP6**




NEXTSPEED® Ascent Category 6 Panel Kits

19-inch, Black, COBRA-LOCK jacks included

Format	24-Port	48-Port
Standard	HPJ624	HPJ648
Angled	HPJ624A	HPJ648A

Complete the Channel with Hubbell Cable and Cords



NEXTSPEED® Category 6E Enhanced UTP Cable

1000 feet, NVP: Plenum 70%, Riser 68%

Color	Cat 6E Plenum Spool	Cat 6E Riser Spool
Blue	C6ESPB	C6ESRB
White	C6ESPW	C6ESRW
Yellow	C6ESPY	C6ESRY

Visit our website for cable requirements and additional colors.



NEXTSPEED® Link 6 UTP Cable

1000 feet, NVP: Plenum 70%, Riser 68%

Color	Link 6 Plenum REELEX® Box	Link 6 Riser REELEX® Box
Blue	HC6RPEB	HC6RREB
White	HC6RPEW	HC6RREW
Yellow	HC6RPEY	HC6RREY

Visit our website for cable requirements and additional colors.



NEXTSPEED® Category 6 Patch Cords

Color	Catalog No.	Color	Catalog No.
Black	HC6BKyy	White	HC6Wyy
Blue	HC6Byy	Yellow	HC6Yyy
Gray	HC6GYyy		

yy = Standard Length: **01** (1'), **03** (3'), **05** (5'), **07** (7'), **10** (10'), **15** (15'), **20** (20'); made-to-order lengths available up to 100ft

Additional colors: **GN** (Green), **OR** (Orange), **PK** (Pink), **P** (Purple), **R** (Red)



NEXTSPEED® Category 6 Low Diameter Patch Cords

Color	Catalog No.	Color	Catalog No.
Black	HCL6BKyy	White	HCL6Wyy
Blue	HCL6Byy	Yellow	HCL6Yyy
Gray	HCL6GYyy		

yy = Standard Length: **01** (1'), **03** (3'), **05** (5'), **07** (7'), **10** (10'), **15** (15'), **20** (20'); made-to-order lengths available up to 100ft

Additional colors: **GN** (Green), **OR** (Orange), **PK** (Pink), **P** (Purple), **R** (Red)