

## HUBBELL 2X2 USB Work Surface Pop-Up Box

- Simple push-down method for opening and closing
- Two 125V receptacles plus two USB charging ports
- 3 Amps of USB charging
- Minimal 5" square footprint
- Brushed aluminum or black powder coat finishes
- Pre-wired, 5' cord, NEMA 5-15P



Charging convenience at the push of a button

Hubbell has developed the UL listed 2X2 USB Work Surface Pop-Up Box. Ideal for work surfaces, such as desks, which require power for a computer and USB charging for smart devices. Developed with coordination from the hotel industry, the Hubbell Pop-Up Box utilizes a pneumatic spring for providing a smooth action for opening and closing. Available in brushed aluminum or black powder coat, the Pop-Up Box is suited for installation with any modern décor.

Two 15A, 125V receptacles and two total 3A USB ports are supplied in this one device, reducing the need for multiple receptacles and minimizing work surface intrusions.

Installation is simple and only requires a jig-saw or similar saw plus a screwdriver. The unit is supplied with a 5 foot cord with a molded plug end allowing it to be installed with ease. Designed to be installed into existing desks or by a furniture manufacture. The Hubbell 2X2 USB Work Surface Pop-Up Box is ideally suited for any work surface application.

### FEATURES

- 15A duplex with two USB charging ports, 3A charging capacity
- 5', pre-wired, 12 gauge, 3 wire electrical cord - making it excellent for conference rooms or classrooms that are frequently rearranged
- Tamper-resistant receptacle
- Gas-spring actuation for smooth opening and closing
- Die cast aluminum construction
- Rated for +10,000 open/close cycles
- Simple three-screw installation
- Unobtrusive low profile flange at 0.05"
- LED power-indicating light
- Easily replaceable receptacle

### SPECIFICATIONS

- cULus
- Listed to UL962A for Furniture Power Distribution Units



# HUBBELL WIRING SYSTEMS

## ORDERING INFORMATION

### 2X2 USB WORK SURFACE POP-UP BOX

Surface Dimensions	Cut out dimensions	Product Depth	Maximum Surface Thickness	Finish	Catalog Number
5" x 5"	4.62" x 4.62"	3.55"	1.125"	Brushed Aluminum	<b>WSBUSB2X2ALU</b>
5" x 5"	4.62" x 4.62"	3.55"	1.125"	Black Powder Coat	<b>WSBUSB2X2BLK</b>

### ELECTRICAL SPECIFICATIONS

Voltage	Current	USB Charging Current	Plug Type	Cord Length
125V	15A	3A	NEMA 5-15P	5 Feet



### DIMENSIONS Inches (mm)

