

*Charging convenience
at the push of a button*

*Simple push-down method
to open and close*

*Brushed aluminum, black powder
coat, or white powder coat finishes*

Easy to install



Hubbell's UL Listed 2X2 USB Work Surface Pop-Up Boxes are ideal for work surfaces, such as desks, which require power for a computer and USB charging for smart devices. Each box includes one 125V, 15A duplex receptacle and two USB ports, available with one Type A and one Type-C or with two Type A ports.

Developed with coordination from the hotel industry, the Hubbell Pop-Up Box utilizes a pneumatic spring for providing a smooth action for opening and closing. Available in brushed aluminum, black powder coat or white powder coat, the Pop-Up Box is suited for installation with any modern décor, making it excellent for conference rooms or classrooms that are frequently rearranged.

Installation is simple and only requires a jig-saw or similar saw plus a screwdriver. The unit is supplied with a 5 foot cord with a molded plug end, allowing it to be installed with ease. Designed to be installed into existing desks or by furniture manufacturers. The Hubbell 2X2 USB Work Surface Pop-Up Box is ideally suited for any work surface application.

FEATURES

- 15A, 125V tamper-resistant duplex receptacle with 2 USB charging ports
- 5A, 5V or 3.8A, 5V USB charging capacity
- 5', pre-wired, 12 gauge, 3 wire electrical cord—excellent for conference rooms or classrooms that are frequently rearranged
- Gas-spring actuation for smooth opening and closing
- Die cast aluminum construction
- Rated for +10,000 open/close cycles
- Simple three-screw installation
- Low 0.070" tapered flange height
- LED power-indicating light

LISTINGS

- cULus listed
- Listed to UL962A for Furniture Power Distribution Units

APPLICATIONS

- Conference rooms
- Classrooms
- Flexible spaces
- Hotels



USB 2X2 Work Surface Pop-Up Box

HUBBELL[®]
Wiring Device-Kellems

2X2 USB Work Surface Pop-up Boxes


Description	Finish	USB Type A & C, 5A-5V USB Output	USB Type A Only, 3.8A-5V USB Output
15A 125V, NEMA 5-15 duplex receptacle with (2) USB charging ports, 5 foot long cord with NEMA 5-15 plug	Brushed Aluminum	WSBUSB2X2AC5ALU	WSBUSB2X2ALU
	Black Powder Coat	WSBUSB2X2AC5BLK	WSBUSB2X2BLK
	White Powder Coat	WSBUSB2X2AC5WHT	-

UL File Number E327832.



Work Surface Pop-up Box Specifications

Maximum Surface Thickness	Cut Out Dimensions	Surface Dimensions	Tapered Flange Height	Product Depth	Cord Length
1.125"	4.62" x 4.62"	5" x 5"	0.070"	3.55"	5 Feet



**Simply push
to open and close**



HUBBELL[®]
Wiring Device-Kellems

www.hubbell.com/wiringdevice-kellems

