HUBBELL
Wiring Device-Kellems

Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 4-Wire, 10A 600V AC, PA Wire Code, 30′ Length

By Hubbell Wiring Device-Kellems
Catalog # PF1004PA030

Signal And Control, Linkosity, Cordset, Female, Single End, Straight, 4-Wire, 10A 600V AC, PA Wire Code, 30′ Length

Features

- Linkosity
- Cordset
- Female
- Single End

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PF1004PA030
Color	Gray
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Female Plug Single Ended Straight
Jacket	PVC
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585243047

Dimensions

Diameter Live Part	.46″

Conductor Related

Conductor Type	Copper
Number of Conductors	4-Pole

Logistics

Carton Quantity	5

Product Assets

Catalogs - WDK Catalog Full 2024
Installation Manuals - WIRING_PD2038_INSTALLINST
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Literature - Linkosity Wiring System
Specifications - PF1004PA030
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved