HUBBELL
Wiring Device-Kellems

Linkosity, 30A Male, Right Angle Cable, 5′

By Hubbell Wiring Device-Kellems
Catalog # PN3004PA005

Linkosity, 30A Male, Right Angle Cable, 5′

Features

- Linkosity
- 30A Male
- Right Angle Cable
- 5′

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PN3004PA005
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Single Ended Cable with Male 90 Degree Connector
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116976

Dimensions

Outside Diameter	0.75

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	4-Pole
Strands	Multi

Logistics

Carton Quantity	10

Product Assets

Catalogs - WDK Catalog Full 2024
Engineering Drawing - PN3004PA005 AutoCAD Drawing
Installation Manuals - WIRING_PD2034_INSTALLINST
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Literature - Linkosity Wiring System
Sales Drawings - WDK_PN3004PA005_DRAWING_PDF
Specifications - PN3004PA005
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved