HUBBELL
Wiring Device-Kellems

Linkosity, 20A Single, Male Female Right Angle Cable, 5′

By Hubbell Wiring Device-Kellems
Catalog # PS2304PB005

Linkosity, 20A Single, Male Female Right Angle Cable, 5′

Features

- Linkosity
- 20A Single
- Male Female Right Angle Cable
- 5′

Application

Quick Connect/Disconnect Signal and Control

General

Catalog Number	PS2304PB005
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	Double Ended Cable with 2) 90 Degree Connectors
OEM Brand Name	Hubbell Wiring Device-Kellems
Plug Type	Linkosity
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585116822

Dimensions

Outside Diameter	0.75

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V kV

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number of Conductors	4-Pole
Strands	Multi

Logistics

Carton Quantity	5

Product Assets

Catalogs - WDK Catalog Full 2024
Engineering Drawing - PS2304PB005 AutoCAD Drawing
Installation Manuals - WIRING_PD1996_INSTALLINST
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Literature - Linkosity Wiring System
Sales Drawings - WDK_PS2304PB005_DRAWING_PDF
Specifications - PS2304PB005
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved