HUBBELL
Wiring Device-Kellems

Switches and Lighting Controls, Combination Devices, Residential Grade, 2) Single Pole Toggles, 15A 120V AC, Self Grounding, Side Wired, Brown

By Hubbell Wiring Device-Kellems
Catalog # RC101AL

Switches and Lighting Controls, Combination Devices, Residential Grade, 2) Single Pole Toggles, 15A 120V AC, Self Grounding, Side Wired, Brown

Features

- Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

Application

Residential

General

Action	Snap Switch
Actuator	Toggle
Catalog Number	RC101AL
Contact Configuration	Two Position
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Switch Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	2) Single Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
UPC	883778109805

Dimensions

Display Size	Standard Size

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Wattage	1800

Logistics

Carton Quantity	10

Product Assets

Catalogs - WDK Catalog Full 2024
Engineering Drawing - RC101AL AutoCAD Drawing
Installation Manuals - WIRING_PD2132_INSTALLINST
Sales Drawings - WDK_RC101_DRAWINGS_PDF
Specifications - RC101AL
Warranty - tradeSELECT™ and netSELECT®

©2024 Hubbell Incorporated. All rights reserved