


Multi-Hole Cord Grip Connectors


Designed with OEMs in Mind

When multiple cables need to be terminated into an enclosure or other piece of equipment, multi-hole cord connectors from Hubbell provide the ideal solution. By having the ability to manage up to four cables through a single connector, space, time, and cost savings can be achieved.



APPLICATIONS

- Control panels
- Robotics
- Enclosure assemblies
- Industrial equipment
- VFD and PLC
- Conveyor belts
- Signal cables
- Motors and generators



Multi-Hole Cord Grip Connectors

Multi-hole Cord Connectors Ordering Info Table

NPT Thread Size	Max. # Holes	Hole Diameter inches (mm)	Material	SKU
1/2"	2	0.23-0.29" (5.8-7.4mm)	Aluminum	MHC1022
3/4"	4	0.23-0.29" (5.8-7.4mm)	Aluminum	MHC1032
1/2"	2	0.23-0.29" (5.8-7.4mm)	Nylon Gray	MHC1022CR
1/2"	2	0.23-0.29" (5.8-7.4mm)	Nylon Black	MHC2022CR
3/4"	4	0.23-0.29" (5.8-7.4mm)	Nylon Gray	MHC1032CR
3/4"	4	0.23-0.29" (5.8-7.4mm)	Nylon Black	MHC2032CR

Hubbell offers solutions to meet all strain relief requirements

Cord Connectors

Description	Cord Diameter inches (mm)	Color Code	Machined Aluminum	Nylon Gray	Nylon Black
Straight male, 1/2" NPT size; form size 2	.13"-.19" (3.2-.4.7)	Orange	SHC1020	SHC1020CR	—
	.19"-.25" (4.7-6.3)	Red	SHC1021	SHC1021CR	SHC2021CR
	.25"-.38" (6.3-.9.7)	White	SHC1022	SHC1022CR	SHC2022CR
	.38"-.50" (9.7-12.7)	Blue	SHC1023	SHC1023CR	SHC2023CR
	.50"-.63" (12.7-15.9)	Brown	SHC1024	SHC1024CR**	SHC2024CR**



Note: IP66 Suitability when used with optional metal clad O-ring. | **Cable jacket may have to be stripped to pass through connector body.

Kellems® Deluxe Cord Grips

Description	NPT Thread Size	Diameter Range Inches (cm)	Catalog Number
Straight male thread	3/8 in.	.250"-.312" (.63-.79)	07401001
		.375"-.437" (.95-1.11)	07401003
	1/2 in.	.187"-.250" (.47-.63)	07401004
		.375"-.500" (.95-1.27)	07401008 07401010
90° male thread	1/2 in.	.250"-.375" (.63-.95)	07401076
		.375"-.500" (.95-1.27)	07401078
45° male thread	3/4 in.	.500"-.625" (1.27-1.59)	074011049
		.625"-.750" (1.59-1.90)	074011051



Use the Kellems® App from Hubbell

- » Quickly identify and choose Kellems® grips, cord connectors and liquid-tight devices
- » View related products
- » Access spec sheets and detailed product information.*
- » [Click here to learn more](#)

Try it today



*Active internet connection required.