

netSELECT® Flat Panel Connection Enclosure
Infrastructure for Digital Lifestyles

- High density delivery of power, data and AV
- Stud or sheetrock mounting flexibility
- Steel construction for residential MDU and commercial applications
- Easily reconfigured to adapt to new applications

FEATURES

- 2- or 4-gang enclosures with 1½" and 1¼" conduit knockouts
- Stud or sheetrock mounting integrated into the enclosure. No need for extra hardware
- ABS trim ring quickly cleans up sheetrock rough-in
- Aesthetically pleasing and durable white powder coated steel base
- Optional screw on cover reduces tampering and protects connections
- 2-gang version mounts to hollow standard two cavity masonry blocks with optional adaptor
- Position between studs in new construction applications with optional mounting brackets

SPECIFICATIONS

- Mechanical
 - 18 gauge cold rolled steel base
 - White powder coat finish
 - High impact ABS trim ring


STANDARDS/LISTINGS/VERIFICATIONS

- cULus 1863 listed
- UL V0 flame rating on ABS trim ring

Accepts Standard Electrical Boxes

1½" and 1¼" Conduit Knockouts

Multiple Device Mounting Options



Trim Ring Covers Rough-In

Integrated Cable Management

Easily Mounts to Studs or Sheetrock

Hubbell netSELECT® FPTV connection enclosure delivers high-density connectivity and power in the wall. In-wall connections allow flat panel displays and interactive smartboards to sit flush without dangling cords. It quickly installs to studs or sheetrock without additional components or hardware.

The enclosure is designed to accommodate large bend radii associated with current cable types such as HDMI, DVI, RG6/UQ, and VGA. The base is constructed from 18 gauge cold rolled steel, which provides toughness and meets requirements for high-rise residential and commercial construction. The white powder coat finish provides durability and an appearance that blends into the wall.

APPLICATIONS

- Interactive whiteboards
- Flat panel displays
- Home theater
- Information displays
- Small wireless APs
- Multimedia workstations



ORDERING INFORMATION


FPTV Connection Enclosure

Description	Color	Catalog Number
2-gang in-wall enclosure	White	NSAV62M
2-gang cover w cable exit	White	NSAV6C
2-gang blank cover	White	NSAV6CB
2-gang block wall adaptor	White	NSAV6BW
4-gang in-wall enclosure	White	NSAV124M
4-gang cover w cable exit	White	NSAV12C
New work stud brackets	-	NSAV6NW



DIMENSIONS

NSAV62M



ACCESSORIES

Power Kits


Description	Color	Catalog Number
Standard Power Kit	White	NSOKPTR
Surge Protected Power Kit	Blue	NSOKPS

Unloaded Plates and Frames

Description	Color	Catalog Number
1-G Blank Plate	White	NP14W
1-G Decorator Plate	White	NP26W
1-G iSTATION Plate	White	IMF1W
1-G 4-Port Keystone Plate	White	NSP14W



NSAV124M




AV Connectors and Plates

Description	Color	Catalog Number
1-Port HDMI Frame	White	NS801W
2-Port HDMI Frame	White	NS802W
HDMI Snap Fit	Black	SFHC14BK
F-Connector Snap Fit	White	NSF70W
USB A-to-B Snap Fit	White	SFUSBABW
Cat 6 Snap Fit Jack	White	NSJ6W

MOUNTING OPTIONS

Mounts to Sheetrock



Mounts to Studs



TYPICAL APPLICATION

INTERACTIVE WHITE BOARD EXAMPLE

