HUBBELL
Wiring Device-Kellems

Lamp Holders and Sockets, Medium Base, Pull Chain, 600W 125V, 5-15R Receptacle, Terminal Screws, Porcelain

By Hubbell Wiring Device-Kellems
Catalog # RL8822

Lamp Holders and Sockets, Medium Base, Pull Chain, 600W 125V, 5-15R Receptacle, Terminal Screws, Porcelain

Features

- Medium Base
- Pull Chain
- 600W 125V
- 5-15R Receptacle

Application

Porcelain Lamp Holders, Medium Base

General

Catalog Number	RL8822
Color	White
EU RoHS Indicator	Yes
Item Type	Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Lampholders
Specifications	• Material - Porcelain • Product Type - Porcelain White Lampholders
Type	Porcelain
UPC	883778112096

Electrical Ratings

Amperage Rating	5.28 A
Connectivity	2) Terminal Screws
Current / Amperage Rating	5.28 A
Current Rating	5.28 A
Frequency Rating	60 Hz
Voltage Rating	125 VAC

Certifications And Compliance

Industry Standard(s)	C/US UL Listed

Logistics

Carton Quantity	50

Product Assets

Catalog Page - WDK BB-6 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - RL8822 AutoCAD Drawing
Installation Manuals - WIRING_PD2478_INSTALLINST
Sales Drawings - WDK_RL8822_DRAWING_PDF
Specifications - RL8822
Warranty - tradeSELECT™ and netSELECT®

©2024 Hubbell Incorporated. All rights reserved