HUBBELL
Wiring Device-Kellems

TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Ivory

By Hubbell Wiring Device-Kellems
Catalog # RRD155I

TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 250V, 2-Pole 3-Wire Grounding, 6-15R, Ivory

Features

- Single Decorator Receptacle
- Self Grounding
- 15A 250V

Application

Residential Receptacles

General

Catalog Number	RRD155I
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	883778300677

Dimensions

Display Size	Standard Sized Product

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	250V kV
Voltage Rating Description	250V kV
Wattage	3750

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	6-15R

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK Z-5 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - RRD155I AutoCAD Drawing
Installation Manuals - WIRING_PD2282_INSTALLINST
Sales Drawings - WDK_RRD155_DRAWING_PDF
Specifications - RRD155I
Warranty - tradeSELECT™ and netSELECT®
Video - Tradeselect Devices

©2024 Hubbell Incorporated. All rights reserved