HUBBELL
Wiring Device-Kellems

Replaced By GFRTW15GRY - Heavy Duty Commercial Weather Resistant AUTOGUARD® Self-Test GFCI Receptacle, 15A, Gray

By Hubbell Wiring Device-Kellems
Catalog # GFTWRST15GY

Power Protection Devices, Receptacle, Self Test, GFCI, TRWR, Commercial Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray.

Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

General

Catalog Number	GFTWRST15GY
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Standard
UPC	883778122583

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-15R

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK K-7 Catalog Page
Catalog Page - WDK Z-8 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - GFTWRST15GY AutoCAD Drawing
Installation Manuals - WIRING_PD2082_INSTALLINST
Literature - AUTOGUARD® Self Test Ground Fault Receptacles
Literature - Connexion 2.0 Zone Distribution System
Sales Drawings - WDK_GFTWRST15_DRAWINGS_PDF
Specifications - GFTWRST15GY
Specifications - Wiring GFTWRST15GY Specification Sheet
Warranty - Industrial & Commercial Products
Video - Autoguard GFCI Receptacles
Video - Tamper-Resistant Receptacles
Video - Tradeselect Devices

©2024 Hubbell Incorporated. All rights reserved