HUBBELL
Wiring Device-Kellems

Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, Black, In NEMA 1 Non Metallic Enclosure

By Hubbell Wiring Device-Kellems
Catalog # HBL1392

Circuit-Lock® NEMA 1 Enclosure Toggle Switch Disconnect, 2-Pole, 30A 600V AC, Thermoplastic.

Features

- Thermoplastic cover on a plated steel base
- Durable, non-conductive cover
- Wiring conduit knockouts
- ½" and ¾" NPT
- Top, bottom or back wire entry points
- Surface mount control
- Switch can be locked in the OFF position as a method of compliance with OSHA lockout/tagout

Performance

- Electrical - Dielectric Voltage - Min. 2,200V AC minimum for 1 minute
- Electrical - Electrical Life - Min. 6,000 Cycles at rated switch load
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94HB/VO
- Environmental - Operating Temperature - Max. 75°C,Min. -40°C continuous w/o impact
- Mechanical - Mechanical Life - Min. 10,000 minimum cycles
- Mechanical - Switch Rating - 25 inch pounds
- Mechanical - Terminal Accommodations - #10 AWG Max
- Mechanical - Terminal Torque - 20 inch pounds
- Mechanical - Wire Type - Solid and stranded copper wire only

General

Catalog Number	HBL1392
Construction	Fabricated
EU RoHS Indicator	No
Enclosure Type	NEMA 1
Horsepower - Maximum	15
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Series	Non-Fused
Specifications	Enclosure Material - Thermoplastic
Style	Standard Duty
UPC	783585680927

Dimensions

Dimensions	4.52 in x 3.97 in x 3.43 in
Display Size	Standard Sized Product
Height	3.43 in
Length	4.52 in
Weight	1.5 lb
Width	3.97 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute
Phase	Single Phase
Wattage	18000 W

Certifications And Compliance

Industry Standard(s)	• CSA-C22.2 No.14 Industrial Control File LR-46186 • UL 508, Industrial Control File #E70402

Logistics

Carton Quantity	10

Product Assets

Brochures - Circuit-Lock® Motor Disconnects
Catalog Page - WDK F-22 Catalog Page
Catalog Page - WDK F-19 Catalog Page
Catalog Page - WDK F-17 Catalog Page
Catalog Page - WDK F-26 Catalog Page
Catalog Page - WDK F-24 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - HBL1392 AutoCAD Drawing
Installation Manuals - WIRING_PD2018_INSTALLINST
Literature - WLFDS011-CANEN

Literature - WLFDS011-CANFR
Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Literature - Safety Product Guide
Literature - Wiring Device Solutions for Strategic Manufacturing Facilities
Literature - 30A Manual Motor Controllers
Sales Drawings - WDK_HBL1392_DRAWING_PDF
Specifications - Wiring HBL1392 Specification Sheet
Specifications - HBL1392 Specification Sheet French
Warranty - Industrial & Commercial Products
Video - Circuit-Lock® Rounded Sloped Top Motor Disconnects

A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL1392-SPEC-EN | REV 10/2024