HUBBELL
Wiring Device-Kellems

Metal PlugTrak, 15A 2 Circuit, 6 Receptacle, 6′ Length, Gray

By Hubbell Wiring Device-Kellems
Catalog # HBL20GBA612GY

Metal PlugTrak, 15A 2 Circuit, 6 Receptacle, 6′ Length, Gray.

Features

- Multiple spacing configurations
- Gray or ivory scratch resistant finish
- Insulation displacement wiring provides superior wire retention

Performance

- Electrical - Receptacle Rating - NEMA 5-15R and NEMA 5-20R
- Mechanical - Wire - #12 AWG Stranded Copper

General

Catalog Number	HBL20GBA612GY
EU RoHS Indicator	Contact Manufacturer
Item Type	Pre-Wired PlugTrak
Number of Receptacles	6
Series	Metal
Specifications	• Number of Receptacles - 6 Singles • PlugTrak Amperage - 15A • PlugTrak Length - 6 Foot • Receptacle Face - Thermoplastic • Spacing - 12 Inch OC • Wiring Type - Hard Wired
Style	Standard
UPC	783585214740

Dimensions

Length	6 ft

Electrical Ratings

Current / Amperage Rating	15 A

Conductor Related

Wire Size	#12 AWG THHN

Certifications And Compliance

Industry Standard(s)	• CSA Standard C22.2 no. 62 • E253976 /E253830 /E253833 • UL Standard UL 5

Logistics

Carton Quantity	2

Product Assets

Catalog Page - WDK S-51 Catalog Page
Catalog Page - WDK S-12 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - HBL20GBA612GY AutoCAD Drawing
Installation Manuals - WIRING_PD2473_INSTALLINST
Sales Drawings - WDK_HBL20GBA612_DRAWING_PDF
Specifications - WIRING_HBL20GBA612GY_spec
Specifications - HBL20GBA612GY Specification Sheet French
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved