HUBBELL
Wiring Device-Kellems

Locking Devices, Twist-Lock®, Valise, Male Plug, 15A 277V AC, 2-Pole 3-Wire Grounding, L7-15P, Screw Terminal, Yellow

By Hubbell Wiring Device-Kellems
Catalog # HBL4773VY

Twist-Lock® Valise® Male Plug, 15A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-15P, Screw Terminal Nylon.

Features

- Two captive multiple drive assembly screws
- Totally insulated impact and crush resistant nylon body
- Powerful cord grips prevent conductor slippage and strain on wiring terminals

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - HB or better per UL 94 or CSA 22.2 No. 0.6
- Environmental - Moisture Resistance - IP20 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #18 AWG - #12 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL4773VY
Cord Range	0.220"-0.660"(5.6-16.8)
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	2
Item Type	15A Valise® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	• Assembly Screws - Steel - Zinc plated • Blades - Brass • Cable Inserts - Polyphenylene Oxide • Housing - Nylon • Terminal Clamp - Cold rolled steel – nickel plated • Terminal Screws - #6-32 Brass (Phillips / Slotted / Robertson)
UPC	783585236933

Dimensions

Dimensions	1.50 in x 1.50 in x 1.87 in
Display Size	Standard Sized
Height	1.87 in
Length	1.5 in
Weight	0.15 lb
Width	1.5 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	277 VAC
Voltage Rating Description	277 VAC

Conductor Related

Cable Range	0.220 - 0.660 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

Certifications And Compliance

Industry Standard(s)	• Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
Nema Rating	L7-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK B-12 Catalog Page
Catalogs - WDK Catalog Full 2024
Installation Manuals - WIRING_PD1237_INSTALLINST
Sales Drawings - WDK_HBL4773V_DRAWING_PDF
Specifications - Wiring HBL4773VY Specification Sheet
Specifications - HBL4773VY Specification Sheet French
Warranty - Industrial & Commercial Products

A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved