HUBBELL
Wiring Device-Kellems

Straight Blade Devices, Male Plug, Valise Series, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15P, White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # HBL8013V

Straight Blade Devices, Male Plug, Valise Series, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5- 15P, White, Single Pack.

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2000V AC minimum
- Environmental - Flammability - UL 94 HB
- Environmental - IP Suitability - IP20
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #18 to #16 AWG
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL8013V
Color	White
Cord Range	0.300"-0.360" (7.6-9.1)
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Valise Plug
Material	Nylon
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hospital Grade
Specifications	• Assembly Screws - Plated Steel • Blades - Brass • Cable Inserts - PPO • Housing - Nylon
Style	• Valise • Insulation Displacement
UPC	783585016177

Dimensions

Dimensions	1.6 in x 1.24 in x 1.17 in
Height	1.17 in
Length	1.6 in
Weight	0.1 lb
Width	1.24 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #16 AWG

Certifications And Compliance

Industry Standard(s)	• Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK A-37 Catalog Page
Catalog Page - WDK L-11 Catalog Page

Catalogs - WDK Catalog Full 2024
Installation Manuals - WIRING_PD1459_INSTALLINST
Literature - Duct Products Guide
Sales Drawings - WDK_HBL8013V_DRAWING_PDF
Specifications - HBL8013V Specification Sheet French
Specifications - Wiring HBL8013V Specification Sheet
Warranty - Industrial & Commercial Products

A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved