HUBBELL
Wiring Device-Kellems

Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1-1/4", 100 feet

By Hubbell Wiring Device-Kellems
Catalog # G1125

Kellems Wire Management, Liquidtight System, Non-Metallic PolyTuff® I Conduit, Gray, 1-1/4", 100 feet

Application

- UL1660

Performance

- Electrical - Voltage Rating - 600V Maximum
- Environmental - Operating Temperature - Dry Env. 0°F to +140°F (-18°C to +60°C)
- Environmental - Operating Temperature - Oil Env. 0°F to +158°F (-18°C to +70°C)
- Environmental - Operating Temperature - Wet Env. 0°F to +140°F (-18°C to +60°C)

General

Catalog Number	G1125
Color	Gray
EU RoHS Indicator	Yes
Finish Type	Smooth
Item Type	Standard Product
Load Capacity	Extra Flexible
Material	Co-extruded rigid and flexible PVC
Specifications	• Bend Radius Inches (mm) - 6.30" (158.8) • Conduit ID/OD Inches (mm) - 1.40"/1.65" (35.4/41.8) • Material - Co-extruded rigid and flexible PVC • Trade Size - 1 1/4 Inch
Type	PolyTuff® I Liquidtight Conduit
UPC	783585333663

Dimensions

Length	100 ft
Trade Size	1 1/4
Width	1.65 in

Electrical Ratings

Voltage Rating	600 V

Certifications And Compliance

Industry Standard(s)	• Meets Requirements Of NEC • UL Listed 1660. Approved For Outdoor And Direct Burial
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	100
Pallet Quantity	600

Product Assets

Catalogs - WDK Catalog Full 2024
Literature - Wire Management Solutions Brochure
Specifications - G1125
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved