HUBBELL
Wiring Device-Kellems

Kellems Wire Management, Liquidtight System, Straight Male Type A Connector, 1/2″, Steel

By Hubbell Wiring Device-Kellems
Catalog # H050CNK

Kellems Wire Management, Liquidtight System, Straight Male Type A Connector, 1/2″, Steel

Performance

- Environmental - Flammability - UL 94-HB and UL 94-V2
- Environmental - Hazardous Location - Suitable for use in hazardous locations per Class I, Div. 2, Class II, Div. 1 & 2, Class III, Div. 1 & 2
- Environmental - Operating Temperature - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	H050CNK
EU RoHS Indicator	Contact Manufacturer
Material	Steel Fitting, Stainless Steel Mesh
Series	Liquidtight Conduit
Specifications	• Conduit Trade Size - 1/2 Inch • NPT Fitting Size - 1/2 Inch • Strand - Stainless Steel • Strand Length - 4.5″ (11.43)
Style	For UL Type A
Type	Straight With Male Fitting
UPC	783585334790

Dimensions

Conduit Trade Size	1/2 in

Certifications And Compliance

Industry Standard(s)	UL Listed

Logistics

Carton Quantity	10

Product Assets

Catalogs - WDK Catalog Full 2024
Literature - Wire Management Solutions Brochure
Specifications - H050CNK
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved