HUBBELL
Wiring Device-Kellems

PS, IEC, PLUG, 2P3W, 30A 550VDC, MAT MOD

By Hubbell Wiring Device-Kellems
Catalog # HBL330P8V0DC

PS, IEC, PLUG, 2P3W, 30A 550VDC, MAT MOD

General

Catalog Number	HBL330P8V0DC
Color	Black
Number Of Poles	2-Pole
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstand 3000V AC Electrical - Max. Working Voltage - 600V RMS Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17 Environmental - Ingress Protection - IP67 Suitability Environmental - Moisture Resistance - Watertight per IEC 60309-1 Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum - 40°C w/o impact Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682 Mechanical - Product Identification - Ratings are a permanent part of the device housing Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions
Series	DC Rated
Style	Standard Service
Type	Watertight Plug
UPC	783585242279

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Voltage Rating	550 VDC
Voltage Rating Description	550 VDC

Conductor Related

Number Of Wires	3-Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified File LR280C UL Classified to IEC 60309-1 IEC 60309-2 UL Listed, File E146033

Product Assets

Catalogs - WDK Catalog Full 2024
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved