HUBBELL
Wiring Device-Kellems

Kellems Wire Management, Liquidtight System, PolyTuff® Non-Metallic Liquidtight Fittings, 90 Degree Male Liquid-Tight Connector, 1/2″, Gray

By Hubbell Wiring Device-Kellems
Catalog # P0509NGY

Kellems Wire Management, Liquidtight System, PolyTuff® Non-Metallic Liquidtight Fittings, 90 Degree Male Liquid-Tight Connector, 1/2″, Gray

Application

- Fittings are to be used with PolyTuff® I and PolyTuff® II

Performance

- Environmental - Flammability - UL 94X-2
- Environmental - Operating Temperature - –30°F to +225°F (–34°C to +107°C)

General

Catalog Number	P0509NGY
Color	Gray
EU RoHS Indicator	Yes
Material	Nylon
Specifications	• Fitting - Nylon • Lockwasher - Zinc plated steel • Sealing Ring - Elastomer
Style	90°
Type	PolyTuff® Non-Metallic Liquidtight Fittings
UPC	783585810010

Dimensions

Dimension - L Length Overall mm	2.91 in
Dimension - Thread Size	1/2″ NPT
Height	1.98 in
Trade Size	1/2

Certifications And Compliance

Industry Standard(s)	• CSA Certified • UL Listed:UL50 Type 4X, 12 and 13
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Pallet Quantity	5400

Product Assets

Catalogs - WDK Catalog Full 2024
Literature - Wire Management Solutions Brochure
Specifications - P0509NGY
Warranty - Industrial & Commercial Products

©2024 Hubbell Incorporated. All rights reserved