NEMA 12 Filter Fan 48 Volt DC 82 Cubic Feet Per Minute 9.8X9.8 - Black

By Wiegmann
Catalog # FF101082CFM48VB

NEMA 12 Filter Fan 48 Volt DC 82 Cubic Feet Per Minute 9.8X9.8 - Black

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

- Ventilation
- Temperature Control

General

Catalog Number	FF101082CFM48VB
Color	Black
Cutout	8.81x8.81
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886746

Dimensions

Actual Depth	4.9 in
Actual Height	9.8 in
Actual Width	9.8 in
Depth	5 in
Height	10 in
Width	10 in

Electrical Ratings

Voltage Rating	48 VDC

Certifications And Compliance

Certified Listed	UL/cUL Recognized

Logistics

Carton Quantity	10

Product Assets

Brochures - Environmental Controls - Thermal Products
Catalogs - Wiegmann Environmental Controls
SDS - HCC SDS
Specifications - FF101082CFM48VB
Terms and Conditions - HCC Terms & Conditions

©2024 Hubbell Incorporated. All rights reserved