NEMA 12 Top Filter Fan 120 Volt 288 Cubic Feet Per Minute 12.8X12.8 Light Gray

By Wiegmann
Catalog # FFTM288CFM115VG

NEMA 12 Top Filter Fan 120 Volt 288 Cubic Feet Per Minute 12.8X12.8 Light Gray

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

- Ventilation
- Temperature Control

General

Catalog Number	FFTM288CFM115VG
Color	Gray
Cutout	6.89x6.89
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886951

Dimensions

Actual Depth	3.7 in
Actual Height	12.8 in
Actual Width	12.8 in
Depth	4 in
Height	13 in
Width	13 in

Electrical Ratings

Voltage Rating	115 VAC

Certifications And Compliance

Certified Listed	UL/cUL Recognized

Logistics

Carton Quantity	1

Product Assets

Brochures - Environmental Controls - Thermal Products
Catalogs - Wiegmann Environmental Controls
SDS - HCC SDS
Specifications - FFTM288CFM115VG
Terms and Conditions - HCC Terms & Conditions

©2024 Hubbell Incorporated. All rights reserved