

# NEW PATRIOT® PATCUT954HS

Long Reach, Live Line, Hydraulic Cable Cutter

## PATCUT954HS Series

### Introduction



#### Introducing the BURNDY® PATRIOT® PATCUT954HS Long Reach, Live Line, Hydraulic Cable Cutter Series.

A new addition to the PATRIOT line of long reach cable cutting tools, the PATCUT954HS Hot Stick Cable Cutter (available in 82" and 94" lengths) provides users both increased flashover protection and extended reach for live line cutting. The large capacity C-Head is designed to hook onto conductors, stabilizing the tool for easy cutting, up to 954 kcmil ACSR.

Designed for safety, convenience, and function, the PATCUT954HS series of battery operated tools perform cuts in less than 15 seconds, minimizing exertion and time required when using similar manual or ratchet type models. Bring the control to your fingertips while safely working with hard to reach, energized overhead or underground lines.

The pistol grip and adjustable assist handle allow for extra control when operating overhead, while the rapid advance ram reduces time on live lines, adding to the overall ergonomics and safety of the system. Large on/off triggers and hand grip area enhance the user experience also.

The PATCUT954HS features protected electronic circuitry, the robust and reliable INFINITY DRIVE® transmission, and a patented high-speed hydraulic pump system, retaining the industry-leading performance, speed, and dependability expected from the PATRIOT line of rugged and reliable tools.

Powered by Makita 18 volt lithium-ion batteries for long-lasting power, the PATCUT954HS is multi-Ah capable, accepting 2.0Ah through 6.0Ah sizes. It is offered with a choice of either 3.0Ah or 5.0Ah batteries.

A lifetime warranty on the INFINITY DRIVE is included, along with a 5-year limited warranty for the tool (excluding blades), and a 3-year limited warranty on the batteries and charger.

UPC#	Catalog Number	Description (All tools accept 2.0Ah-6.0Ah Lithium-ion Batteries)
621945541740	PATCUT954HS82LI	82" Tool, 3.0Ah 18V LI, AC charger
621945542631	PATCUT954HS82L5	82" Tool, 5.0Ah 18V LI, AC charger
621945542624	PATCUT954HS82LCB	82" Tool, no batteries or charger
621945541757	PATCUT954HS94LI	94" Tool, 3.0Ah 18V LI, AC charger
621945542655	PATCUT954HS94L5	94" Tool, 5.0Ah 18V LI, AC charger
621945542648	PATCUT954HS94LCB	94" Tool, no batteries or charger

Customer Service 1-800-346-4175 | Tool Service Center 1-800-426-8720 | Technical Services 1-800-451-4956 | [www.burndy.com](http://www.burndy.com)



Connecting Power to Your World®

