



GCS-YA TOWER GROUND CLAMP



The GCSYA_WEEB and GCS2YA series connectors are used to terminate the equipment grounding conductor (EGC) to the tower structure, in applications where drilling or hot permits are either not possible or unwanted. Installation requires no power tools and is simple to install. The GCSYA_WEEB is assembled with a WEEB® Washer to reduce one-hole lug rotation. These connectors can also be used in a variety of other applications outside of tower grounding as it is suitable to bond steel from 1/8”-5/8” thick.

FEATURES AND BENEFITS

- Provides proper grounding of towers
- Easy and simple hex tooling installation
- No hot work permit or drilling required
- Includes compression lug and anti-rotation WEEB Washer for one-hole applications
- Accommodates steel 1/8” TO 5/8” thick
- Conductor range from #8 AWG to #2 AWG
- UL467 Listed
- AT&T Approved



Material Description	Description
GCSYA8CWEEB	8AWG - Single Hole Clamp - Accommodates steel 1/8” TO 5/8” thick
GCSYA62CWEEB	6AWG - Single Hole Clamp - Accommodates steel 1/8” TO 5/8” thick
GCSYA4CWEEB	4AWG - Single Hole Clamp - Accommodates steel 1/8” TO 5/8” thick
GCSYA2CWEEB	2AWG - Single Hole Clamp - Accommodates steel 1/8” TO 5/8” thick
GCS2YA8C	8AWG - Two Hole Clamp - Accommodates steel 1/8” TO 5/8” thick
GCS2YA6C	6AWG - Two Hole Clamp - Accommodates steel 1/8” TO 5/8” thick
GCS2YA4C	4AWG - Two Hole clamp - Accommodates steel 1/8” TO 5/8” thick
GCS2YA2C	2AWG - Two Hole clamp - Accommodates steel 1/8” TO 5/8” thick



burndy.com

For product inquiries, please contact your BURNDY® Customer Service Representative at 1-800-346-4175, Tooling Service Center 1-800-426-8720, or Technical Services 1-800-451-4956.

©2021 Hubbell Incorporated.
Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.
Printed in the U.S.A.

5STAR PRICING

WEEB-ONE-HOLE

TRADE

5STAR

FQ

UPC #	Material #	Material Description	Price/e	Price/e	Price/e
62194563580	50114561	GCSYA8CWEEB	\$48.12	\$33.68	\$26.94
62194563582	50114562	GCSYA6CWEEB	\$51.33	\$35.93	\$28.74
62194563583	50114563	GCSYA4CWEEB	\$48.61	\$34.03	\$27.22
62194563585	50114565	GCSYA2CWEEB	\$49.24	\$34.47	\$27.58


TWO-HOLE

TRADE


5STAR

FQ

UPC #	Material #	Material Description	Price/e	Price/e	Price/e
62194563950	50116895	GCS2YA8C	\$49.58	\$34.71	\$27.77
62194563951	50116896	GCS2YA6C	\$49.86	\$34.90	\$27.92
62194563993	50116897	GCS2YA4C	\$50.55	\$35.39	\$28.31
62194563995	50116899	GCS2YA2C	\$49.94	\$34.96	\$27.97



GCSYA_WEEB



GCS2YA



burndy.com



For product inquiries, please contact your BURNDY® Customer Service Representative at 1-800-346-4175, Tooling Service Center 1-800-426-8720, or Technical Services 1-800-451-4956.

©2021 Hubbell Incorporated.
Because Hubbell has a policy of continuous product improvement, we reserve the right to change design and specifications without notice.
Printed in the U.S.A.