NEMA 4X Hinge Cover Wire Trough 2.5 X 2.5 X 12 in. 304 Stainless Steel

By Wiegmann
Catalog # T2212CHSS

*Representative Image

NEMA 4X Hinge Cover Wire Trough 2.5 X 2.5 X 12 in. 304 Stainless Steel

Features

- Trough and cover are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Easy to operate external clamps and continuous hinge are provided
- External mounting feet are included
- Cover is sealed with a poured in place gasket

General

Catalog Number	T2212CHSS
Cover Type	Hinged Cover
EU RoHS Indicator	No
Finish Type	Grained Stainless Steel
Latches Type	External Clamps
Material	304 Stainless Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	T_CHSS
UPC	786725888504

Dimensions

Actual Depth	12.31 in
Actual Height	4 in
Actual Width	4 in
Depth	12 in
Height	2.5 in
Weight	4.9 lb
Width	2.5 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	1, 12, 4 & 4X

Logistics

Carton Quantity	1

Product Assets

3D Models - T2212CHSS
Catalogs - Wiegmann WIreways & Fittings
Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice
Engineering Drawing - HWDT2212CHSS-S
Sales Drawings - HWDT2212CHSS-S
SDS - HCC SDS
Sell Sheets - T-CHSS Series Stainless Steel Wiring Trough
Specifications - T2212CHSS
Terms and Conditions - HCC Terms & Conditions

©2024 Hubbell Incorporated. All rights reserved