

LET'S GET BACK TO WORK TOGETHER!

GET A FREE CUTTING JAW

WHEN YOU BUY A
PATMD-LW CRIMPER KIT
WITH NEW NYLON PRO BAG:

Qualifying Models for FREE* Cutter Jaw	Crimp Jaw, Battery
Catalog#	
PATMD10003A3	BG/D3, 3Ah
PATMD10005A3	BG/D3, 5Ah
PATMD20003A3	D3, 3Ah
PATMD20005A3	D3, 5Ah
PATMD30003A3	O/D3, 3Ah
PATMD30005A3	O/D3, 5Ah

NOTE: Qualifying models include crimper, two batteries, charger, lanyard, and nylon pro bag.

***Conditions Apply:**

- Proof of Sale is required.
- Offer Valid September 1, 2020 through November 30, 2020.
- Cannot be combined with any other offer or special pricing. Prior sales excluded.



ACSR Cutter Jaw



CU/AL Cutter Jaw



EHS GUY Cutter Jaw



**IN THE MOST CHALLENGING TIMES,
BURNDY HAS YOUR BACK!**

CUTTING CAPACITIES	ACSR	ALUMINUM (AAC)	COPPER (SOFT DRAWN)	EHS GUY
ACSR Jaw	556.5 kcmil	636 kcmil	350 kcmil	-
CU/AL Jaw	636 kcmil	636 kcmil	600 kcmil	-
EHS GUY Jaw	-	-	-	3/8"

CRIMPING CAPACITIES	TERMINALS & SPLICES	TAPS
Copper	#8 - 500 kcmil	#10 - 2/0 AWG
Copper Flex	#8 - 350 kcmil	
Aluminum (AAC)	#8 - 350 kcmil	#14 - 4/0 AWG



1-800-346-4175 | www.burndy.com



LET'S GET BACK TO WORK TOGETHER!

FREE JAW OFFER

CHECK FREE JAW CHOICE:



End Customer Name: _____

Company Name: _____

Shipping Address: _____

Phone Number (with area code): _____

Email: _____

BURNDY Salesperson: _____

Email Completed Form and Distributor Invoice to: lpayette@burndy.com

***Conditions Apply:**

- Valid for new orders only, placed 9/1/2020 through 11/30/2020.
- All prior sales excluded.
- Allow 2 weeks for order processing.
- Completed Form and Distributor Invoice for tool must be received **no later than 12/31/2020** to receive free jaw.

Qualifying Models for FREE* Cutter Jaw	
Catalog#	Crimp Jaw, Battery
PATMD10003A3	BG/D3, 3Ah
PATMD10005A3	BG/D3, 5Ah
PATMD20003A3	D3, 3Ah
PATMD20005A3	D3, 5Ah
PATMD30003A3	O/D3, 3Ah
PATMD30005A3	O/D3, 5Ah

CUTTING CAPACITIES	ACSR	ALUMINUM (AAC)	COPPER (SOFT DRAWN)	EHS GUY
ACSR Jaw	556.5 kcmil	636 kcmil	350 kcmil	-
CU/AL Jaw	636 kcmil	636 kcmil	600 kcmil	-
EHS GUY Jaw	-	-	-	3/8"

CRIMPING CAPACITIES	TERMINALS & SPLICES	TAPS
Copper	#8 - 500 kcmil	#10 - 2/0 AWG
Copper Flex	#8 - 350 kcmil	
Aluminum (AAC)	#8 - 350 kcmil	#14 - 4/0 AWG



1-800-346-4175 | www.burndy.com

