

Hubbell-PRO Hospital Grade ● Tamper-Resistant Receptacles

- Patented TR design eliminates plug-in difficulty and TR complaints
- Fed-Spec UL listing insures proven performance in demanding applications
- Perfect for pediatric care, waiting rooms, medical offices and other institutional applications where safety and performance are critical



Features

- For use in NEC® locations requiring Tamper-Resistant receptacles
- Best-in-class TR mechanism
- Fed-Spec UL listed
- Engineered, Designed, and Assembled in USA
- Tested to UL Hospital Grade test standards for impact resistance and abrupt plug pull-out
- NAFTA and Trade Act Compliant

APPLICATIONS

- Pediatric Hospitals
- Medical Offices
- Psychiatric Care Facilities
- Healthcare OEM

The Hubbell Tamper-Resistant Mechanism eliminates the frustration and difficulty experienced using TR receptacles with plugs that have sharp, or bent blades. Hubbell TR receptacles work so well there is virtually no perceptible difference in the feel between the TR receptacles and our conventional non-TR receptacles. Trust Hubbell to deliver Tamper-Resistant protection that feels like it's not even there.




Tamper-Resistant... **NOT** Plug Resistant™




Hubbell-PRO Hospital Grade ● Tamper-Resistant Receptacles



Hubbell-PRO Hospital Grade ● Tamper-Resistant Receptacles

Description	Color	Duplex		Style Line® Decorator	
		15A 125V	20A 125V	15A 125V	20A 125V
Smooth nylon face, back and side wired 	Black	8200BKTRA	8300BKTRA	2172BKTRA	2182BKTRA
	Brown	8200TRA	8300TRA	2172TRA	2182TRA
	Gray	8200GYTRA	8300GYTRA	2172GYTRA	2182GYTRA
	Ivory	8200IVTRA	8300IVTRA	2172IVTRA	2182IVTRA
	Light Almond	8200LATRA	8300LATRA	2172LATRA	2182LATRA
	Red	8200REDTRA	8300REDTRA	2172REDTRA	2182REDTRA
	White	8200WTRA	8300WTRA	2172WTRA	2182WTRA
LED, smooth nylon face, back and side wired  	Black	8200BKLTRA	8300BKLTRA	2172BKLTRA	2182BKLTRA
	Brown	8200LTRA	8300LTRA	2172LTRA	2182LTRA
	Gray	8200GYLTRA	8300GYLTRA	2172GYLTRA	2182GYLTRA
	Ivory	8200IVLTRA	8300IVLTRA	2172IVLTRA	2182IVLTRA
	Light Almond	8200LALTRA	8300LALTRA	2172LALTRA	2182LALTRA
	Red	8200REDLTRA	8300REDLTRA	2172REDLTRA	2182REDLTRA
	White	8200WLTRA	8300WLTRA	2172WLTRA	2182WLTRA



LED Power Indicators

Used most often to identify emergency circuits in hospitals, the two LED power indicators are bright enough to be visible in low light and bright daylight conditions and identify Boss with power.

Tamper-Resistant

Compliant with NEC® 406.12 and NEC® 517-18(c), SNAPConnect® Tamper-Resistant Receptacles are acceptable for use in residential dwellings and pediatric locations.

Also available in Commercial and Residential Receptacles.

Visit the Hubbell online catalog for more information (www.hubbell-wiring.com/catalog.aspx).

Additional Hospital Products

Hospital Grade Nightlight GFCIs and USB Charger Receptacles

Color	Nightlight GFCI		USB Charger	
	15A 125V AC	20A 125V AC	15A 125V AC	20A 125V AC
Black	GFRST82BKNL	GFRST83BKNL	USB8200BK	USB8300BK
Brown	GFRST82NL	GFRST83NL	USB8200	USB8300
Gray	GFRST82GYNL	GFRST83GYNL	USB8200GY	USB8300GY
Ivory	GFRST82INL	GFRST83INL	USB8200I	USB8300I
Light Almond	GFRST82LANL	GFRST83LANL	USB8200LA	USB8300LA
Red	GFRST82RNL	GFRST83RNL	USB8200R	USB8300R
White	GFRST82WNL	GFRST83WNL	USB8200W	USB8300W

