WILEYBRAID24, Cu Braid , 24.00 IN L, 0.709 IN W, M6 or 1/4" Hardware NOT included

By WILEY
Catalog # WILEYBRAID24

Cu Braid , 24.00 IN L, 0.709 IN W, .257 IN Hole Dia.

Application

The corrosion resistant, tin plated copper Wiley line of bonding jumpers are high quality solutions for your system to create an electrical bond between two pieces of galvanized or other uncoated electrically conductive metals. Standard lengths range from 6" to 36", with or without installation hardware assembled or unassembled. Custom lengths are also available on request. UL467 and UL2703 Listed.

General

Catalog Number	WILEYBRAID24
Item Type	3B
Trade Name	WILEY
UPC	781810565629
UPC 12 Digit	7818105656299

Dimensions

Bolt Size	1/4 in
Dimension - Thread Size	-

Certifications And Compliance

Certification - CSA Approved	N
Certification - ETL	Y
Certification - UL Recognized	N
Certification - cULus	N
Certified Listed	UL2703
Industry Standard(s)	UL2703
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	50
Pallet Quantity	8400

Product Assets

Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Certifications - UL Standard for Safety for Grounding & Bonding Equipment, UL 467, CSA C22.2 No. 41-13
Certifications - UL Certificate of Compliance, UL 2703
Customer Notices - Prop 65 Notice
Sales Drawings - 50033063
Specifications - WILEYBRAID24

©2024 Hubbell Incorporated. All rights reserved