

## **NexLED**



The **NexLED** delivers an instant bright white light. Designed for low profile applications, the bulkhead can be mounted on walls, handrails and ceilings making it ideal for walkways or restricted height areas.

The **NexLED emergency** option provides emergency battery backup to ensure continued operation in the event of a power outage. Benefits from the same features as the standard NexLED and is also available as a low temperature version for operation down to -45°C.

## **Mounting Options**

- Ceiling
- Wall
- Recessed
- Pole/Stanchion
- Bulkhead











## **Standard Specification**

- N	lex			г

TOTAL DELD						
Enclosure	Aluminium LM6 body, RAL-9005 black epoxy polyester paint finish with toughened glass and silicone gasket					
Reflector	Brushed aluminium					
Entry	3 x M20 cable entries					
Termination	3 core 4mm² max conductor with looping (4 core on Emergency)					
Installation	Surface mounted, 4 mounting holes located outside of seal					
Control Gear	Electronic Driver					
Colour Temperature (CCT)	4100K (Neutral White)					
Maintenance	M6 Slotted Screws					
Battery	Internal NiMH (201-6V, 801-10.8V) (Emergency only)					
<b>Emergency Light Duration</b>	3 Hours (100% output)					
Ingress Protection	IP66/67 to EN 60529					
Surge Protection	4kV					
Electrical Supply	120-240V AC 50/60HZ 220-254V AC 50/60Hz (Emergency only)					

## **Features**

- Highly visible, instant light
- Easy to install and maintain
- Ultra long life, no re-lamping required
- Over 60,000 hours\* continuous operation
- 100% output in emergency mode (up to 3 hours)
- Very low power consumption
- Highly Energy Efficient
  - \* 60,000 hours expected at 40°C ambient (L70/B10)





Std. Cat No.	Delivered Output	Power Consumption	Ambient °C	Weight
NELI/201/LE	168 lm	7W	-20 to +45	3.5kg
NELI/801/LE	671 lm	16W	-20 to +45	3.5kg
NELI/201/LE/EM	168 lm	8W	-20 to +45	4.1kg
NELI/801/LE/EM	671 lm	17W	-20 to +45	4.1kg

Options - Suffix to Catalogue No.


/GDE Green LED's (should not be used in combination with Exit sign)


**Accessories** Accessories should be ordered separately


Order Code

Green Exit sign kit (supplied with up, down, left and right labels\*)

**SNEL1-0008** 







Product design and specification: are subject to change without notice. Please check the Chalmit website for latest specifications.

www.chalmit.com













 $<sup>{\</sup>it *Other signage options available upon request, please contact Chalmit} {\it *sales}.$