




FITTINGS



# KILLARK<sup>®</sup> EZ SEAL

Next Generation of  
Hazardous-Rated Seal Fittings




# Your solution to the world's most frustrating problems when pouring seals!

Killark's patent pending EZ Seal offers the fastest and safest way to pour vertical seal fittings for hazardous area conduit systems. Its revolutionary design requires virtually zero pre-pour preparation.


The EZ Seal is the only seal-off on the market that allows for 360 degrees of unimpeded access to the conductors with minimal packing fiber required to dam the seal.

No more tooling or frustrating attempts to separate the wires during the prepping process due to limited space. Use everyone's favorite two-part epoxy resin, CELOX™, as the compound solution for fastest results.

The seal is installed like most standard seals, but what makes it EZ is...




- 1 Install your conduit seal and pull wires
- 2 Pull the EZ tab then unscrew the middle coupler, and slide it down to access the potting chamber
- 3 The disc brush nylon fibers will act as a dam for your SC Compound or CELOX to be poured
- 4 Slide middle coupler back up, tighten, then replace the EZ Tab with "seal poured" indication



Class I, Div. 1 & 2, Groups A, B, C, D  
 Class I, Zone 1, Groups IIC, IIB, IIA  
 Class II, Div. 1 & 2, Groups E, F, G  
 Class III  
 Type 3R

EZ SEAL SERIES (VERTICAL SEALS ONLY)									
HUB SIZE	CATALOG NUMBER			DIMENSIONS					
	ALUMINUM	ZINC PLATED STEEL	316 STAINLESS STEEL	A	B	C	D	E	TURN RADIUS
1/2"	EZ 1	EZ 1S	EZ 1SS	4.45	1.60	3.15	5.45	1.06	0.80
3/4"	EZ 2	EZ 2S	EZ 2SS	4.44	1.60	3.15	5.76	1.15	0.80
1"	EZ 3	EZ 3S	EZ 3SS	5.08	1.96	3.60	6.24	1.15	0.98

**EZ Seal offers the same solution as up to 3 seals... and it's RETROFITTABLE!**





## Complimentary products

Class I, Div. 1 & 2, Groups A, B, C, D  
 Class II, Div. 1 & 2, Groups E, F, G  
 Class III



**Save the hassle of prepping compound by using CELOX™ quick sealing resin.**

- Two-part epoxy resin, self-mixed through a patented nozzle
- Eliminates waste as each tube is reusable
- Cures faster in colder climates
- Single tube style design for simple use
- Replacement nozzles and dispensing guns available

**Combine the world's fastest compound, CELOX, with the new EZ Seal and you have the fastest installed seal on the market!**

CELOX SEALING COMPOUND	
CATALOG NUMBER	PACKAGE SIZE
KQS-050 ML	50 ml (1.7 oz)
KQS-250 ML	250 ml (8.45 oz)

*\*includes 4 static mixing nozzles*

DISPENSING GUN	
CATALOG NUMBER	CARTRIDGE SIZE
KQS-050 GUN	50 ml Cartridge
KQS-250 GUN	250 ml Cartridge

REPLACEMENT NOZZLES	
CATALOG NUMBER	NOZZLE SIZE
KQS-050 NOZ	50 ml Cartridge Nozzle (5 per)
KQS-250 NOZ	250 ml Cartridge Nozzle (5 per)

CELOX KIT	
CATALOG NUMBER	KIT INCLUDES
KQS-050 KIT	(4) 50 ml Cartridges (16) Mixing Nozzles (1) Dispensing Gun (1) 4oz Packing Fiber



# The Next Generation of Vertical Seal Fittings

