



Tri-Power Pop-Up Receptacle

Quick Installation Setup Guide

Key Benefits

- Available in seven different finishes
- Water and tamper-resistant face
- Compact shallow design minimizes space in cabinet
- cULus Listed for countertop installation
- Easy push-down to pop-up function is rated for a minimum of 10,000 cycles (OPEN/CLOSE)
- Permanent installation ready (suitable for AC90 or NMD 90 wire)

Before Installing the Countertop Receptacle:

Different components will be used throughout the installation including the housing, base, countertop flange, receptacle cover, locking nut and installation screws.



www.hubbell.ca



Step 1

Cut a circular hole approximately 4" in diameter in the countertop.

Then, determine what colour silicone top to use, peel off the protective tab to expose adhesive surface on the pop-up tower, snap on that cover. For black colour RCT600BK & RCT620BK and white colour RCT600W & RCT620W, skip this step, go to step 2.



Step 2

Remove the base from the housing to expose screw terminals.



Step 3

CAUTION:
Before handling the cable, make sure the circuit is OFF.

Place the tightening ring on the cable whip before wiring the device.

Feed cable through the lock nut under the countertop, as this will secure the device later.



Step 4

Fasten the metal jacket to the device base. A fitting will be required (not included).






Quick Installation Setup Guide

Because Spills Happen

Hubbell countertop receptacles are spill test compliant

COUNTERTOP RECEPTACLES

Description	Finish	Color/ Material	15A 125V Receptacle		20A 125V Receptacle	
			Surface Mount	Flush Mount	Surface Mount	Flush Mount
Tamper-resistant pop-up kitchen counter receptacle, rated for 20A circuits	Powder Coated	Black	RCT200BK	RCT201BK	RCT220BK	RCT221BK
		White	RCT200W	RCT201W	RCT220W	RCT221W
		Bronze	RCT200BZE	RCT201BZE	RCT220BZE	RCT221BZE
Cover: machined aluminum, wiring chamber accepts AC90 or NMD wire	Brushed	Aluminum	RCT200ALU	RCT201ALU	RCT220ALU	RCT221ALU
		Brass	RCT200BR	RCT201BR	RCT220BR	RCT221BR
		Nickel	RCT200NI	RCT201NI	RCT220NI	RCT221NI
	Polished	Chrome	RCT200CH	RCT201CH	RCT220CH	RCT221CH
Tri-power AC, includes: tamper-resistant pop-up kitchen counter receptacle, USB Type AC and wireless inductive, rated for 20A circuits	Powder Coated	Black	RCT600BK	—	RCT620BK	—
		White	RCT600W	—	RCT620W	—
		Bronze	RCT600BZE	—	RCT620BZE	—
Cover: machined aluminum, wiring chamber accepts AC90 or NMD wire	Brushed	Aluminum	RCT600ALU	—	RCT620ALU	—
		Brass	RCT600BR	—	RCT620BR	—
		Nickel	RCT600NI	—	RCT620NI	—
	Polished	Chrome	RCT600CH	—	RCT620CH	—



HUBBELL CANADA

870 Brock Road South • Pickering, ON L1W 1Z8
Phone (905) 389-1138 • FAX (905) 839-9108 • www.hubbell.ca

Printed in Canada. Specifications subject to change without notice. ® is a registered trademark of Hubbell Incorporated.



H3843 01/22