


Split Loom Tubing / Tefzel Cable Ties

Organize and Protect



Split Loom

Product material: Polyethylene (PE)

Operating Temperature: 40°F to +199°F (-40°C to +93°C)

Structure: corrugated both inner and outer

Color: Black

Features and Benefits

- Split loom is ideal for applications where braided tubing or spiral wrap may be difficult to install
- Tubing provides full coverage where spiral wrap or other coverings may not be suitable
- In harsh applications the tubing provides resistance to crushing, impact, and abrasion
- Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires



TEFZEL® Cable Ties

Product material: TEFZEL® Fluoropolymer

Operating Temperature:

Min: -112°F (-80°C) Max: 338°F (170°C)

Color: Aqua Blue

Features and Benefits

- Low smoke density with excellent flammability rating (UL 94V-0)
- Curved tip for ease of installation
- For indoor or outdoor use
- Tolerates extreme high and low temperatures

TEFZEL® is Registered trademark of E.I. du Pont de Nemours and Company

UPC	Catalog Number	Description	Trade Price	5 Star
621945499843	LOOM75	3/4" Diameter X 328 FT, Polyethylene Black Tubing	72.16 per roll	50.51 per roll
621945499850	LOOM100	1" Diameter X 164 FT, Polyethylene Black Tubing	75.70 per roll	52.99 per roll
621945499867	LOOM150	1.50" Diameter X 164 FT, Polyethylene Black Tubing	116.42 per roll	81.49 per roll
621945499874	LOOM200	2.00" Diameter X 82 FT, Polyethylene Black Tubing	96.96 per roll	67.87 per roll
621945514195	CTZ18075C6	Tefzel Cable Tie, Blue, Tensile 18 lb., Bundle Diam .87", Length 4.00" 100 pcs	42.93 per 100 pcs	30.05 per 100 pcs
621945514201	CTZ18125C6	Tefzel Cable Tie, Blue, Tensile 18 lb., Bundle Diam 1.39", Length 6.25" 100 pcs	93.20 per 100 pcs	65.24 per 100 pcs
621945514188	CTZ30200C6	Tefzel Cable Tie, Blue, Tensile 30 lb., Bundle Diam 2.00", Length 4.00" 100 pcs	122.17 per 100 pcs	85.52 per 100 pcs
621945514218	CTZ50175C6	Tefzel Cable Tie, Blue, Tensile 50 lb., Bundle Diam 1.75", Length 7.75" 100 pcs	178.60 per 100 pcs	125.02 per 100 pcs
621945514423	CTZ50300C6	Tefzel Cable Tie, Blue, Tensile 50 lb., Bundle Diam 3.00", Length 11.00" 100 pcs	284.30 per 100 pcs	199.01 per 100 pcs
621945514430	CTZ50400C6	Tefzel Cable Tie, Blue, Tensile 50 lb., Bundle Diam 4.00", Length 14.50" 100 pcs	390.07 per 100 pcs	273.05 per 100 pcs
621945514447	CTZ100300C6	Tefzel Cable Tie, Blue, Tensile 100 lb., Bundle Diam 3.00", Length 11.00" 50 pcs	204.09 per 100 pcs	142.86 per 100 pcs
621945514454	CTZ100400C6	Tefzel Cable Tie, Blue, Tensile 100 lb., Bundle Diam 4.00", Length 14.50" 50 pcs	266.40 per 100 pcs	186.48 per 100 pcs

Customer Service 1-800-346-4175 | Tool Service Center 1-800-426-8720 | Technical Services 1-800-451-4956 | www.burndy.com



Connecting Power to Your World®

