

U•CONDUIT™

10-IN-1

UNIVERSAL CONDUIT BODY for RIGID/IMC or EMT

Configures to all standard bodies
(LB, LR, LL, T, C)

Space Saver!
& Trip Saver!

Easily swap panels for
any configuration

Captive Screws

Attached O-ring

Patented self-aligning
covers/panels

Combo hubs compatible
with all conduit types


Seamless
pre-affixed gasket

Reducer bushings for smaller
conduit/fittings*

UCB050

Comes pre-configured for LB/LL

Features

- Patented interchangeable panels can be configured to LB, LR, LL, T or C
- Suitable for weatherproof installs
- Use set screws for EMT conduit, and threaded hubs for threaded Rigid/IMC conduit or fittings
- Available in trade sizes 1/2", 3/4" and 1"
- Lightweight, Durable TAYMAC TUFF® Die-cast Aluminum Construction
- Seamless pre-affixed gasket and self-aligning covers/panels
- More wiring capacity than standard bodies and meets 2014 NEC 314.16(C)(2) for volume marking
- Tri-combo head set screws 
- Unique design lends to easy, time-saving installations
- Captive screws with attached O-ring for ease of use and a weatherproof seal
- Includes 4 steel reducer bushings in the 1" size – (2) 1" to 3/4", (2) 1" to 1/2"; and (2) 3/4" to 1/2" bushings in the 3/4" size*.
- Not suitable for use in hazardous location applications
- Includes (1) body, (3) blank covers/panels, (1) T panel, (1) LL/LB/LR panel, reducer bushings*, (1) closure plug and extra hardware
- Ideal for service trucks and reduces inventory

* 1/2" trade size does not include reducer bushings.




NEC & NEMA 3
Compliant


US Patent 8,242,386 B1




U•CONDUIT™ – Universal Conduit Body easily configures for all common uses




LL/LB



LR/LB



T



C



UCB075

CATALOG #	DESCRIPTION	VOLUME	PKG. TYPE	STD. PKG.	UPC	I 2 of 5
U•CONDUIT™ 10-IN-1 UNIVERSAL CONDUIT BODY						
UCB050	1/2" Universal Conduit Body	5.8 cu in (95 cc)	Shrink Wrap	10	050169571224	50050169571229
UCB075	3/4" Universal Conduit Body	9.5 cu in (156 cc)	Shrink Wrap	10	050169571231	50050169571236
UCB0100	1" Universal Conduit Body	14.3 cu in (234 cc)	Shrink Wrap	10	050169571248	50050169571243