



WIEGMANN®

Commercial and Industrial Enclosures

NEMA 4X Stainless Steel Screw Cover Enclosures



WA-GSCSS SERIES SCREW COVER ENCLOSURES

CAT. NUMBER 304	CAT. NUMBER 316	ENCLOSURE SIZE H x W x D
WA060604GSCSS	WA060604GSCSSA	6.00x6.00x4.00 (152x152x102)
WA060606GSCSS	WA060606GSCSSA	6.00x6.00x6.00 (152x152x152)
WA060804GSCSS	WA060804GSCSSA	6.00x8.00x4.00 (152x203x102)
WA060806GSCSS	WA060806GSCSSA	6.00x8.00x6.00 (152x203x152)
WA080804GSCSS	WA080804GSCSSA	8.00x8.00x4.00 (203x203x102)
WA080806GSCSS	WA080806GSCSSA	8.00x8.00x6.00 (203x203x152)
WA081004GSCSS	WA081004GSCSSA	8.00x10.00x4.00 (203x254x102)
WA101004GSCSS	WA101004GSCSSA	10.00x10.00x4.00 (254x254x102)
WA101006GSCSS	WA101006GSCSSA	10.00x10.00x6.00 (254x254x152)
WA101206GSCSS	WA101206GSCSSA	10.00x12.00x6.00 (254x305x152)
WA121204GSCSS	WA121204GSCSSA	12.00x12.00x4.00 (305x305x102)
WA121206GSCSS	WA121206GSCSSA	12.00x12.00x6.00 (305x305x152)
WA121606GSCSS	WA121606GSCSSA	12.00x16.00x6.00 (305x406x152)
WA121608GSCSS	WA121608GSCSSA	12.00x16.00x8.00 (305x406x203)
WA161606GSCSS	WA161606GSCSSA	16.00x16.00x6.00 (406x406x152)
WA161608GSCSS	WA161608GSCSSA	16.00x16.00x8.00 (406x406x203)
WA181806GSCSS	WA181806GSCSSA	18.00x18.00x6.00 (457x457x152)
WA202008GSCSS	WA202008GSCSSA	20.00x20.00x8.00 (508x508x203)
WA202408GSCSS	WA202408GSCSSA	20.00x24.00x8.00 (508x610x203)
WA242406GSCSS	WA242406GSCSSA	24.00x24.00x6.00 (610x610x152)
WA242408GSCSS	WA242408GSCSSA	24.00x24.00x8.00 (610x610x203)
WA303012GSCSS	WA303012GSCSSA	30.00x30.00x12.00 (762x762x305)
WA363612GSCSS	WA363612GSCSSA	36.00x36.00x12.00 (914x914x305)

Application:

Designed for use as a wiring box, junction box, pull box, and terminal box in many indoor or outdoor applications where dust or moisture is a problem

Features:

- Seams are continuously welded and ground smooth
- 304 and 316 Stainless Steel construction
- Cover contains closed cell oil resistant neoprene gasket
- Enclosure comes with stainless steel screws which thread into sealed wells to prevent liquid, dust, etc from entering the box through the screw holes
- No holes, knockouts, or rear mounting holes

Industry Standards:

UL50, Types 3, 4 and 4X
NEMA/EEMAC Type 3, 4 and 4X



Wiegmann
Freeburg, IL 62243
618-539-3193

WIEGMANN®

© 2020 Hubbell. All rights reserved. Information subject to change.
Trademarks are property of their respective owners.

hubbell.com/wiegmann/en

Hubbell Canada Inc. 905-839-1138
Hubbell de Mexico, S.A. de C.V. 52-55-9151-9999

WG_SEL_008 rev1
1/2020