








# WALL SWITCH








Transform any standard light switch into a connected wall switch and conveniently control lighting and accessories from anywhere.



## WALL SWITCH KEY FEATURES

-  Standard Installation
-  Pull Out Tab
-  Remote Access
-  Voice Control
-  LED Night Light
-  No Hub Required
-  Two-Year Warranty

## ACCESSORIES TO CONTROL WITH WALL SWITCH

-  Recessed Lighting
-  Landscape Lighting
-  Ceiling Fans
-  Entry Lighting
-  Flush Mount Fixtures
-  Pendant Lighting
-  Exterior Lighting

## COMPATIBLE PLATFORMS

-  Works with **Apple HomeKit**
-  WORKS WITH **alexa**
-  works with the **Google Assistant**
-  Works with **IFTTT**

## SPECIAL ORDER CUSTOM COLORS AVAILABLE



## WALL SWITCH FEATURES AND RATINGS

- Fits any standard gang box
- Supports single pole, 3- and 4-way operation
- No hub or running additional wires
- Compatible with most standard bulbs
- Works with any standard rocker faceplate
- Pull-out HomeKit™ pairing tab
- Customizable LED night light
- Input: 120-277VAC, 50/60Hz
- Output: 120-277VAC, 50/60Hz
- Resistive: 1800W @ 120-277VAC, 15A/6.5A
- Tungsten: 960W @ 120VAC, 8A
- Tungsten: 1800W @ 277VAC, 6.5A
- Motor: 1HP @ 120 & 277VAC
- Ballast: 10A @ 277VAC

## CONNECTED APP

The iDevices Connected app allows you to control and schedule all your iDevices products from anywhere, with your iOS or Android™ device.

### App Features:

- Voice control with Siri®, Alexa and the Google Assistant
- Access from anywhere, no hub required
- Set schedules, scenes, and control multiple homes
- Compatible with other HomeKit™ products
- Customize with pictures of your home
- Over-the-air software updates



## SHIPPING SPECIFICATIONS

	Shipping Specs	Product Dimensions	Carton Dimensions
Product Number	IDEV0008		
UPC#	852931005643		
Cube (FT3)	0.17		
Carton UPC#	10852931005640		
Height		4.35"	5.00"
Width		2.00"	5.5"
Depth		2.50"	10.5"
GW		6.4 oz	4.34 lbs
NW			4.06 lbs
Pack Quantity			10

**STANDARDS & CERTIFICATIONS:** UL compliant, FCC compliant, RoHS compliant, CSA compliant, IC compliant, Wi-Fi CERTIFIED™, Bluetooth®

