

Combination Wireless Wall Mount Charger & USB Outlet

Quick Product Facts

Product Launch Summary

Date: November 2019

From: Vic Flagello x4858

email: vflagell@hubbell.com

Product Description:

The Hubbell wireless phone charger transfers energy from the charger to the battery in the phone via electromagnetic induction. The charger uses two induction coils to create an alternating electromagnetic field. The receiver coil in the phone converts back into electricity to be fed into the battery. Using Qi charge technology the wireless charger provides a faster recharge than the standard wireless battery charging technology. The USB Charger is rated 5 amps. The Type C port offers up to 9 volts of USB output for Fast Charge. The USB Type A port offers standard 5 volts.



USB1528AC

Key Feature

Key Benefits

Wireless Charger

Qi Certified:

Wireless Charging:

Dual Coils:

Wattage:

Phone Holder:

Compatible with Qi protocol. Provides safe and reliable wireless charge
Charge phone more efficiently and conveniently
Perfect phone placement. Horizontal or Vertical
7.5W
Securely holds phone with access to home button

Duplex Receptacle

Receptacle Rating:

Tamper Resistant Duplex:

Fast Charge Type A & C ports:

LED Power Indicator:

15A or 20A 125V
Safe and reliant, additional charging capabilities
Blue wireless indicator signifies wireless charging, and proper positioning
Yellow power available LED

Compatible with USB 1.1/2.0/3.0:

Compatible with USB Type A and C devices

Market Strategy:

No Cord No Problem! Ideal solution to cut down on cord clutter in spaces with a high cord volume. Also, this will increase convenience and aesthetic quality. This product is excellent for renovation and remodeling as it replaces a single duplex. Simply install this instead of a duplex at a counter area. Idea for kitchen or lab/nurse work It is perfectly suited for specifications in new commercial construction. Qi certification assure compliance with other wireless devices. This charger can be designed into work stations and areas where phone and electronics are popularly used or stored.


Targets:


Commercial Buildings, Universities, Dormitories, Airports, Hotels, Restaurants, and Residential

Replacement Items:

N/A

Competition:

Legrand  Not Fast Charge

Samsung 

Belkin 

Only Make Wireless plug in desk top pads; No receptacles offering

Complementary Products:

Activity Time Line:

Launch: October, 2019

Applications:

Combination Wireless Wall Mount Charger & USB Outlet is ideal for new residential construction or updating current homes, universities, commercial buildings, hotels, airports, or any other application where fast, reliable, easily accessible charging power is necessary.

Agency Listings:

- Qi Certified
- cULus Listed
- FCC Approved

Specifications:

Electrical:

USB 5 Amp, 5V DC: modulates up to 9 volts
Input voltage: 125V AC, 60Hz
Inductive coil: 7.5 watts

Vocabulary/Industry Terms/FAQ's:

- **Qi** (pronounced 'chee'), is a standard developed by the **Wireless Power Consortium (WPC)** for inductive electrical power transfer over distances of up to 4cm. Products marked as Qi Certified have passed rigorous, independent laboratory tests for safety, interoperability and energy efficiency.
- **Alternative claims** like "Qi compliant," "Qi compatible" or "Works with Qi," suggests a product has not undergone proper Qi certification testing.