

TOP PERFORMANCE AT TOP SPEED



Kurt Versen F & J Xicato
4" Family Downlights
now available in **2 WEEKS!**



50 piece limit per sku, 100 piece limit
per purchase order for two week
lead time.

Please click [HERE](#) for Pricing , Terms & Conditions.



Velocity Quick Ship Program -

Kurt Versen's Xicato based 4" Round and Square Architectural Products.

ORDERING GUIDES:

ROUND 4"

| Base Specification (required) Example: F1334-213012D | | | | | | Options (optional) | | |
|---|---------------|---------------|----------|----------|---|--|---|------------------|
| Application | Model | Source Lumens | Kelvin | Volts | Dimming | Cone Finish | Cone Paint | Support Rails |
| Downlight | F1332* Wide | 11 1100 | 27 2700K | 12 120V | D Standard 0-10V, to 10%. DM1 0-10V to 1%. | Standard Specular clear SS SoftSheen™ S Softglow® | Standard clear WT White Flange. WHT White Cone, complete. BT Black Flange. | R2 26" R5 52" |
| | F1334* Medium | 15 1500 | 30 3000K | 27 277V | | | | |
| | F1336* Narrow | 21 2100 | 35 3500K | 40 4000K | | | | |
| Directional | F2333 Wide | | | | | | | |
| | F2335 Medium | | | | | | | |
| | F2337 Narrow | | | | | | | |
| Wall Wash | F1355 | | | | | | | |

*ENERGY STAR® Certification includes: 3000K, 3500K, 4000K CCT. Standard 83 CRI. Specular and SoftSheen™ Clear. Standard Solite Lens.

SQUARE 4"

| Base Specification (required) Example: J1344-213012D | | | | | | Options (optional) | | |
|---|---------------|---------------|----------|----------|---|--|---|------------------|
| Application | Model | Source Lumens | Kelvin | Volts | Dimming | Cone Finish | Cone Paint | Support Rails |
| Downlight | J1342* Wide | 11 1100 | 27 2700K | 12 120V | D Standard 0-10V, to 10%. DM1 0-10V to 1%. | Standard Specular clear SS SoftSheen™ S Softglow® | Standard clear WT White Flange. WHT White Cone, complete. BT Black Flange. | R2 26" R5 52" |
| | J1344* Medium | 15 1500 | 30 3000K | 27 277V | | | | |
| | J1346* Narrow | 21 2100 | 35 3500K | 40 4000K | | | | |
| Directional | J2333 Wide | | | | | | | |
| | J2335 Medium | | | | | | | |
| | J2337 Narrow | | | | | | | |
| Wall Wash | J1353 | | | | | | | |

*ENERGY STAR® Certification includes: 3000K, 3500K, 4000K CCT. Standard 83 CRI. Softglow® and SoftSheen™ Clear. Standard Solite Lens.