



 **PROGRESS**  
LIGHTING™

**SURFACE MOUNT**

**LED**



# LED SURFACE

The LED Surface Mount series delivers a perfect solution for flush mount and recessed applications, for both **residential** and **commercial markets**. In addition, it is **wet location listed** and a cost-effective solution for **fire rated** applications. The series features a 120V alternating current source & eliminates the need for a traditional LED driver. This modular approach results in an encapsulated luminaire that unites **performance**, **cost** and **safety benefits**.

## FEATURES

- Sleek profile
- Flicker free dimming with many ELV dimmers
- Wet location listed
- 90+ CRI
- 120v input voltage AC
- 60,000 hour life
- 3000K color temperature
- CA Title 24 Compliant

### P8022 SERIES

7-1/4" Round



Antique Bronze

17w: 1035 Lumens, 60 Lumens/watt

P8022-20/30K9-AC1-L10	Antique Bronze
P8022-28/30K9-AC1-L10	White
P8022-31/30K9-AC1-L10	Black
P8022-82/30K9-AC1-L10	Metallic Gray

**Includes:** Flush mount and recessed installation options\*

### P8027 SERIES

7-1/4" Square



Metallic Gray

17W: 1035 Lumens, 60 Lumens/watt

P8027-20/30K9-AC1-L10	Antique Bronze
P8027-28/30K9-AC1-L10	White
P8027-31/30K9-AC1-L10	Black
P8027-82/30K9-AC1-L10	Metallic Gray

**Includes:** Flush mount and recessed installation options\*

### P8222 SERIES

7-1/4" Round



White

17W: 1035 Lumens, 60 Lumens/watt

P8222-28/30K9-AC1-L10	White
-----------------------	-------

**Includes:** Flush mount installation option\*

### P8107 SERIES

5-1/2" Round



Black

12w: 673 Lumens, 56 Lumens/watt

P8107-20/30K9	Antique Bronze
P8107-28/30K9	White
P8107-31/30K9	Black
P8107-82/30K9	Metallic Gray

**Includes:** Flush mount installation option. Requires a 2" minimum depth junction box\*

### P8247 SERIES

5-1/2" Decorative Round



Brushed Nickel

12w: 630 Lumens, 53 Lumens/watt

P8247-20/30K9-AC1-L06	Antique Bronze
P8247-28/30K9-AC1-L06	White
P8247-31/30K9-AC1-L06	Black
P8247-09/30K9-AC1-L06	Brushed Nickel

**Includes:** Flush mount installation option\*

### P8241 SERIES

5-1/2" Square



White

10.5w: 680 Lumens, 65 Lumens/watt

P8241-20/30K9-AC1-L06	Antique Bronze
P8241-28/30K9-AC1-L06	White
P8241-31/30K9-AC1-L06	Black
P8241-82/30K9-AC1-L06	Metallic Gray

**Includes:** Flush mount installation option\*

\*See reverse for installation options



# MOUNTS

## P8147 SERIES

7-1/4" Round



White

17w: 1050 Lumens, 63 Lumens/watt

P8147-20/30K9 Antique Bronze

P8147-28/30K9 White

P8147-31/30K9 Black

P8147-82/30K9 Metallic Gray

**Includes:** Flush mount and recessed installation options\*

## P8240 SERIES

5-1/2" Round



Antique Bronze

12w: 623 Lumens, 52 Lumens/watt

P8240-20/30K9-AC1-L06 Antique Bronze

P8240-28/30K9-AC1-L06 White

P8240-31/30K9-AC1-L06 Black

P8240-82/30K9-AC1-L06 Metallic Gray

**Includes:** Flush mount installation option\*

## SUITABLE FOR A VARIETY OF APPLICATIONS

Residential  
Commercial  
Multi-Family  
Wet Location  
Outdoor

Bathroom  
Shower  
Utility  
Kitchen  
Garage






# INSTALLATION OPTIONS

## Maximum Versatility

Ideal for use in recessed and flush mount applications, the LED Surface Mount Series embraces an installation system that is versatile, simple and seamless. Choose the option below that suits your application.

### Flush Mount





LED Surface Mounts use an intuitive snap-in system that makes flush mount installation easier than ever. Simply install adaptor onto junction box, then snap into place using the flush mount clip. The quick-link wiring system completes the flush mount installation.




Quick-Link


### Recessed



Twist-and-Push Mount



Quick-Link



Quick-Link w/  
E26 Edison Base  
Adapter



E26 Edison Base  
Adapter

The P8022 and P8027 includes an adjustable mounting option that fits 6", 5" or 4" recessed housings. Simply Twist-and-Push into the recessed housing and finish with the quick-link wiring system. The P8022 and P8027 also includes an E26 Edison Base adaptor for a retrofit screw-in option. (available for purchase with other series - 7-1/4" - P8595-01 / 5-1/2" - P8596-01)

**PROGRESS**  
LIGHTING™

701 Millennium Boulevard  
Greenville, SC 29607  
[progresslighting.com](http://progresslighting.com)