



# WIEGMANN®

## Commercial and Industrial Enclosures



# N412 ULTIMATE™ Series Double Door Enclosures

## Get the Ultimate for Harsh Environments!



**NEW!**

Part of our ULTIMATE™ Enclosure line, these double door wall-mount enclosures complement our single door models. Removable, interchangeable doors feature concealed hinges. Removable center post provides easy access to components and for installing back panels. Designed for applications where dirt, dust, oil or water are present.

- Carbon steel construction with continuous welded seams
- Powder coat finish
- Doors sealed with poured-in-place gaskets
- Mounting holes located in the back of the enclosure
- Grounding studs welded to doors and body
- Collar studs for mounting optional ULTIMATE series back panels
- 3-point keylocking/padlocking handle included
- NEMA 4, 3R, 12,13 and IP66

NEMA/EEMAC Type 3R, 4, 12, 13  
UL 508A, Type 3R, 4, 12, 13

cULus certified Type 3R, 4, 12, 13  
IEC 60529, IP66



CAT. NO.	DESCRIPTION	DIMENSIONS H X W X D	BACK PANEL*
N412D243608C	N412 DBL DR Wall Mnt Ult 24 x 36 x 08 CS-Gry	24" x 36" x 8"	NP3624C
N412D244208C	N412 DBL DR Wall Mnt Ult 24 x 42 x 08 CS-Gry	24" x 42" x 8"	NP4224C
N412D244808C	N412 DBL DR Wall Mnt Ult 24 x 48 x 08 CS-Gry	24" x 48" x 8"	NP4824C
N412D304210C	N412 DBL DR Wall Mnt Ult 30 x 42 x 10 CS-Gry	30" x 42" x 10"	NP4230C
N412D304810C	N412 DBL DR Wall Mnt Ult 30 x 48 x 10 CS-Gry	30" x 48" x 10"	NP4830C
N412D306010C	N412 DBL DR Wall Mnt Ult 30 x 60 x 10 CS-Gry	30" x 60" x 10"	NP6030C
N412D364212C	N412 DBL DR Wall Mnt Ult 36 x 42 x 12 CS-Gry	36" x 42" x 12"	NP4236C
N412D364812C	N412 DBL DR Wall Mnt Ult 36 x 48 x 12 CS-Gry	36" x 48" x 12"	NP4836C
N412D366012C	N412 DBL DR Wall Mnt Ult 36 x 60 x 12 CS-Gry	36" x 60" x 12"	NP6036C
N412D424212C	N412 DBL DR Wall Mnt Ult 42 x 42 x 12 CS-Gry	42" x 42" x 12"	NP4242C
N412D424812C	N412 DBL DR Wall Mnt Ult 42 x 48 x 12 CS-Gry	42" x 48" x 12"	NP4842C
N412D426012C	N412 DBL DR Wall Mnt Ult 42 x 60 x 12 CS-Gry	42" x 60" x 12"	NP6042C
N412D484812C	N412 DBL DR Wall Mnt Ult 48 x 48 x 12 CS-Gry	48" x 48" x 12"	NP4848C

\*Back Panels Must Be Ordered Separately

Wall mounting kits are required to maintain cULus external mounting requirements.

Optional N412MFK mounting foot kit must be ordered separately.

**Contact your sales representative today for pricing and ordering details.**



**COMMERCIAL CONSTRUCTION**  
A Division of Hubbell Incorporated (Delaware)

Wiegmann  
Freeburg, IL 62243  
618-539-3193

**WIEGMANN®**

© 2018 Hubbell. All rights reserved. Information subject to change.  
Trademarks are property of their respective owners.

Hubbell Canada Inc. 905-839-1138  
Hubbell de Mexico, S.A. de C.V. 52-55-9151-9999

[hubbell.com/wiegmann/en](http://hubbell.com/wiegmann/en)

WG\_SEL\_021\_N412D  
7/2019