

HUBBELL®
Wiring Device-Kellems

Tamper-Resistant NOT Plug Resistant®



The Industry's Best Tamper-Resistant Receptacle for Healthcare Applications



Jackson Bradley, Design Engineer, Atlanta, GA

I received the receptacles this morning and am really impressed. I walked around the house plugging many different types of devices and all worked very smoothly.

I have been a design engineer for almost 30 years and know a good design when I see it. You can be proud of this one.


- **Hubbell Patented Technology for a Superior Tamper-Resistant Mechanism**
- **Available In 15 and 20 Amp**
- **Assorted Colors**
- **UL, CSA**

The Hubbell Solution

Hubbell's patented Cam Action Technology makes inserting a plug as easy as plugging into a standard receptacle. This design has been incorporated into our Industrial, Hospital, Commercial and Residential receptacles. This broad offering ensures the right quality product for all projects.



Tamper-Resistant - Safety Made Easy



Patented Cam Action Mechanism

The Hubbell product development team engineered a better way to provide tamper-resistance to our receptacles with our patented cam action mechanism. When a plug is inserted into a Hubbell tamper-resistant receptacle, the cam slides the insulating barrier out of the way. The rotating action eliminates friction, creating a smoother, more reliable insertion. As a result, difficulties due to problematic plugs are minimized.



Scan to see how the Patented Cam Action Mechanism works



Hubbell-PRO Hospital Grade • Tamper-Resistant Receptacles

Color	15A 125V		20A 125V		15A 125V		20A 125V		15A 125V		20A 125V	
	Black	8200BKTRA	8300BKTRA	8200BKLTRA	8300BKLTRA	2172BKTRA	2182BKTRA	2172BKLTRA	2182BKLTRA	2172BKTRA	2182BKTRA	2172BKLTRA
Brown	8200TRA	8300TRA	8200LTRA	8300LTRA	2172TRA	2182TRA	2172LTRA	2182LTRA	2172TRA	2182TRA	2172LTRA	2182LTRA
Gray	8200GYTRA	8300GYTRA	8200GYLTRA	8300GYLTRA	2172GYTRA	2182GYTRA	2172GYLTRA	2182GYLTRA	2172GYTRA	2182GYTRA	2172GYLTRA	2182GYLTRA
Ivory	8200IVTRA	8300IVTRA	8200IVLTRA	8300IVLTRA	2172IVTRA	2182IVTRA	2172IVLTRA	2182IVLTRA	2172IVTRA	2182IVTRA	2172IVLTRA	2182IVLTRA
Light Almond	8200LATRA	8300LATRA	8200LALTRA	8300LALTRA	2172LATRA	2182LATRA	2172LALTRA	2182LALTRA	2172LATRA	2182LATRA	2172LALTRA	2182LALTRA
Red	8200REDTRA	8300REDTRA	8200REDLTRA	8300REDLTRA	2172REDTRA	2182REDTRA	2172REDLTRA	2182REDLTRA	2172REDTRA	2182REDTRA	2172REDLTRA	2182REDLTRA
White	8200WTRA	8300WTRA	8200WLTRA	8300WLTRA	2172WTRA	2182WTRA	2172WLTRA	2182WLTRA	2172WTRA	2182WTRA	2172WLTRA	2182WLTRA

SNAPConnect® Hospital Grade • Tamper-Resistant Receptacles

Color	15A 125V		20A 125V		15A 125V		20A 125V		Description	Catalog Number
	Black	SNAP8200BKTRA	SNAP8300BKTRA	SNAP2172BKTRA	SNAP2182BKTRA	Solid	SNAP1RA			
Brown	SNAP8200TRA	SNAP8300TRA	SNAP2172TRA	SNAP2182TRA	Stranded	SNAP2RA				
Gray	SNAP8200GYTRA	SNAP8300GYTRA	SNAP2172GYTRA	SNAP2182GYTRA						
Ivory	SNAP8200ITRA	SNAP8300ITRA	SNAP2172ITRA	SNAP2182ITRA						
Light Almond	SNAP8200LATRA	SNAP8300LATRA	SNAP2172LATRA	SNAP2182LATRA						
Red	SNAP8200RTRA	SNAP8300RTRA	SNAP2172RTRA	SNAP2182RTRA						
White	SNAP8200WTRA	SNAP8300WTRA	SNAP2172WTRA	SNAP2182WTRA						

Also available in Split Circuit and with LED Power Indicators. Visit the Hubbell online catalog for more information.

Hospital Grade • GFCI Receptacles

Also Available in the Hubbell Tamper-Resistant Line

- Standard
- Night Light (with two LED night lights)
- With Alarm
- Tamper-Resistant and Weather Resistant



HUBBELL®
Wiring Device-Kellems

www.hubbell-wiring.com

