

50 Amp Cable Set

With Two High Intensity LEDs:
 "Power-On" and "Incorrect Wiring" Indicators

HUBBELL

Built With The
 Hubbell Quality
 You've Come
 To Expect.



- Two bright, durable, LEDs. GREEN indicates "power-on" and RED indicates "incorrect wiring" at the power source.
- High Intensity LEDs are visible - even in bright sunlight.
- Totally molded design for superior waterproofing and durability.
- Exclusive copper crimp barrel terminations for tighter connections and longer life.



Bull Ring
 for Added
 Strain Relief

Exclusive Crimp
 Termination
 for Longer Life

50A Shore Power Cable Set with Two LED Indicators

Vinyl jacketed shore power cable set. #6 AWG type STOW is completely factory pre-wired with molded-on devices.



50A 125V


Catalog Numbers
 125V



50A 125/250V

Catalog Numbers
 125/250V

Description	Catalog Numbers 125V	Catalog Numbers 125/250V
50 ft. Yellow Shore Power Cable Set.	HBL61CM53LED	HBL61CM52LED
50 ft. White Shore Power Cable Set.	HBL61CM53WLED	HBL61CM52WLED
25 ft. Yellow Shore Power Cable Set.	HBL61CM43LED	HBL61CM42LED
25 ft. White Shore Power Cable Set.	—	HBL61CM42WLED



IP56
 SUITABILITY
 (Boatside)



Printed In U.S.A. Specifications subject to change without notice.
 © Registered trademark of Hubbell Incorporated.
 Hubbell Incorporated (Delaware) • 185 Plains Road • Milford, CT 06461-2420 • (203) 882-4800 • FAX (800) 255-1031

H5199



www.hubbell-marine.com

30 Amp Cable Set

With High Intensity LED "Power-On" Indicator

HUBBELL

Built With The
Hubbell Quality
You've Come
To Expect.



- Bright, durable, LED (green) indicates "power-on".
- High Intensity LED is visible - even in bright sunlight.
- Totally molded design for superior waterproofing and durability.
- Exclusive copper crimp barrel terminations for tighter connections and longer life.



**Bull Ring
for Added
Strain Relief**

**Exclusive Crimp
Termination
for Longer Life**

30A Shore Power Cable Set with LED "Power-On" Indicator

Vinyl jacketed shore power cable set. #10 AWG is factory pre-wired with molded-on devices. Connector end has non-metallic threaded sealing ring which makes inlet/connector interface watertight.




NEMA L5-30
30A 125V

Description	Catalog Numbers
50 ft. Yellow Shore Power Cable Set.	HBL61CM08LED
35 ft. Yellow Shore Power Cable Set.	HBL61CM05LED
25 ft. Yellow Shore Power Cable Set.	HBL61CM03LED
50 ft. White Shore Power Cable Set.	HBL61CM08WLED
35 ft. White Shore Power Cable Set.	HBL61CM05WLED
25 ft. White Shore Power Cable Set.	HBL61CM03WLED



**Bright Green LED
Indicates "Power-On"**



**Ergonomic
Styling**

**Arrows
Line-Up**

IP56
SUITABILITY
(Boatside)

