

# YOUR SAFETY MATTERS.

OUR LATEST IN ILLUMINATED SAFETY TECHNOLOGY, THE 90-MINUTE EMERGENCY EXIT LIGHT, GIVES YOU TIME AND PEACE OF MIND IN A CRISIS.



UP TO 90 MINUTES OF LIGHT



SIMPLE DESIGN WITH EASE OF INSTALLATION



LIMITED WARRANTY



FLAME-RATED UV STABLE THERMOPLASTIC




ADJUSTABLE LED LAMPS



FINISH & TRIM OPTIONS



IDEAL FOR HALLWAYS, CORRIDORS & ENTRYWAYS



WAYSTAR™

SEE REVERSE SIDE FOR MORE INFORMATION, OR VISIT [PROGRESSLIGHTING.COM/WAYSTAR](http://PROGRESSLIGHTING.COM/WAYSTAR)

**PROGRESS**  
LIGHTING™

PL\_1291\_4.18

# WHEN THE POWER IS OUT PROGRESS LIGHTING IS ON.

## INTRODUCING THE WAYSTAR™ 90-MINUTE EMERGENCY EXIT LIGHT

Achieve quality, value and peace of mind with this new compact and attractive LED based emergency light. Housing is a flame-rated UV stable thermoplastic in white and black finish options. The unit has 4 adjustable LED lamps that power on upon power outage for up for 90 minutes giving you time to find safety.

### PRODUCT FEATURES

- Intelligent 2-wire input connection
- External push-to-test switch and AC-on indicator
- Battery re-charge within 24 hours
- AC Lock-out circuit
- Low voltage disconnect
- Conduit entry knock-out located at the top center
- Suitable for IC and Non-IC applications
- Microprocessor controlled pulse charger
- Options for self-diagnostics
- Self-Test feature automatically runs a 1-minute test once a month and an alternating 30 or 60-minute test once every six months. Multi-color LED indicator provides visible fault detection and charging status
- User initiated 1 or 90-minute system test feature
- 15 minute re-transfer delay
- Automatic unit transfer in brownout conditions
- UL924 Listed for damp location
- NFPA 101 and NFPA 70

### RESIDENTIAL



WAYSTAR™ - PECEM-30  
RECTANGLE & ROUND  
TRIMS INCLUDED

FINISH OPTIONS  
○ WHITE  
● BLACK

### COMMERCIAL



WAYSTAR™ - PECEM-31-SD  
RECTANGLE & ROUND TRIMS  
INCLUDED

FINISH OPTIONS  
○ WHITE  
● BLACK