


CATALOG NO.	ITEM NUMBER	DIMENSIONS							
		B ±.08	C ±.04	E ±.02	K DIA. ±.02	L ±.12	N ±.03	T REF.	Z MIN.
YAZV282TC38FXB	26001992	1.77 [45]	1.14 [29]	1.00 [25]	.41 [10]	4.18 [106]	.41 [10]	.15 [4]	.42 [11]
YAZV282TC38E16FXB	30013260	1.77 [45]	1.14 [29]	1.75 [44]	.41 [10]	4.93 [125]	.41 [10]	.15 [4]	.42 [11]
YAZV282NTCFXB	25021988	1.77 [45]	1.14 [29]	1.75 [44]	.56 [14]	5.37 [136]	.62 [16]	.15 [4]	.64 [16]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	07/29/2013	TONGUE MARKING UPDATED	32639	PB	VK

CATALOG NO.	ITEM NUMBER	CONDUCTOR		BOLT SIZE	INSTALLATION TOOLING (# CRIMPS)							WIRE STRIP LENGTH												
		FLEX	CODE (AWG)		DIE INDEX	COLOR CODE	MECHANICAL		HYDRAULIC				DIELESS (# CRIMPS)											
							MD7-34R	OUR840	PAT500 Y500CT	Y750, Y35, PAT35 Y39, PAT750	Y46 4	Y45 3												
YAZV282TC38FXB	26001992	4/0 WELD 550/24	4/0 AWG	3/8 [M10]	15	PURPLE	W28VT W28RT (4)	W28VT W28RT (4)	W28VT W28RT (4)	U28RT (2)	U28RT (2)	U28RT (2)	MECHANICAL: MY29-11 (1) HYDRAULIC: Y644, Y644M Y644MBH, (1) Y81KFT-, PAT81KFT-Y4PC-, PAT4PC-SERIES (1)	1-11/16										
YAZV282TC38E16FXB	30013260																							
YAZV282NTCFXB	25021988			1/2 [M12]																				



**NOTES:**

1. MATERIAL: COPPER TUBING.
2. FINISH: TIN PLATED.
3. CATALOG # PT6515 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y45 SERIES TOOLS.
4. CATALOG # PUADP-1 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 SERIES TOOLS.
5. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
6. CONNECTOR IS UL LISTED.
7. CONNECTOR IS CSA LISTED.

TO ORDER BURNDY® PRODUCTS CALL		HYLUG™ BELLED 4/0 (550/24)													
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE CAT. NO: YAZV28-2---FXB(SEE TABLE)													
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		<table border="1"> <tr> <td>DRAWN BY: D RAJENDRAN</td> <td>3/24/2011</td> </tr> <tr> <td>CHECKER: M JEFF</td> <td>4/12/2011</td> </tr> <tr> <td>DSN APRVL: M JEFF</td> <td>4/12/2011</td> </tr> <tr> <td>MFG APRVL: T THRELFALL</td> <td>4/16/2011</td> </tr> <tr> <td>QA APRVL: T WATTS</td> <td>4/12/2011</td> </tr> <tr> <td>MKT APRVL: --</td> <td></td> </tr> </table>		DRAWN BY: D RAJENDRAN	3/24/2011	CHECKER: M JEFF	4/12/2011	DSN APRVL: M JEFF	4/12/2011	MFG APRVL: T THRELFALL	4/16/2011	QA APRVL: T WATTS	4/12/2011	MKT APRVL: --	
DRAWN BY: D RAJENDRAN	3/24/2011														
CHECKER: M JEFF	4/12/2011														
DSN APRVL: M JEFF	4/12/2011														
MFG APRVL: T THRELFALL	4/16/2011														
QA APRVL: T WATTS	4/12/2011														
MKT APRVL: --															
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		<table border="1"> <tr> <td>PROD FAM: CM&amp;R COMPRESSION</td> <td>DRAWING NO</td> <td>REV</td> </tr> <tr> <td>PROJECT #: --</td> <td>SIZE</td> <td></td> </tr> <tr> <td>DOCUMENT TYPE: SALES</td> <td>30013761</td> <td>B</td> </tr> <tr> <td>REL LEVEL: Released</td> <td>D</td> <td>SHEET 1 OF 1</td> </tr> </table>		PROD FAM: CM&R COMPRESSION	DRAWING NO	REV	PROJECT #: --	SIZE		DOCUMENT TYPE: SALES	30013761	B	REL LEVEL: Released	D	SHEET 1 OF 1
PROD FAM: CM&R COMPRESSION	DRAWING NO	REV													
PROJECT #: --	SIZE														
DOCUMENT TYPE: SALES	30013761	B													
REL LEVEL: Released	D	SHEET 1 OF 1													