


| | | | |
|-------------------------|----------------|----------------|----------------|
| DRAWING NO. 30021187 | | | |
| ITEM NUMBER | CATALOG NUMBER | L | LI |
| 30020044 | BF33D50G87TN | 33.50 [851] | 32.00 [813] |
| 30021194 | BF37D72G87TN | 37.72 [958] | 36.22 [920] |

| REV | DATE | DESCRIPTION | ECO | BY | C'H'K. |
|-----|------------------------|--|-------|----|--------|
| B | 07/10/2015 00:00:00 AM | CHANGE THE ITEM NUMBER FROM 3017914 TO 30020044 AS PER SAP | 40930 | AS | MB |



- NOTES:
- APPROXIMATE AMP RATING: 360A INDOOR, 430A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
 - ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
 - ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING AND BONDING EQUIPMENT STANDARDS.

| | | | |
|---|--|----------------------------------|--|
| TO ORDER BURNDY® PRODUCTS CALL | | BRAID | |
| UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH) | | ITEM NO: SEE TABLE | |
| CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) | | CAT. NO: BF--G87TN (SEE TABLE) | |
| FOR PRODUCT INFO: http://www.burndy.com | | DRAWN BY: T.BALAN 05/18/2011 | |
| | | CHECKER: E.MARTIN 10/19/2011 | |
| | | DSN APPVL: C.RICARDO 10/20/2011 | |
| | | MFG APPVL: -- -- | |
| | | QA APPVL: P.ALEJANDRO 10/19/2011 | |
| | | MKT APPVL: T.PETER 10/19/2011 | |
| | | SCALE: 1:1 | |
| | | DRAWING NO | |
| | | 30021187 | |
| | | REV | |
| | | B | |
| | | SHEET 1 OF 1 | |

REV: PE0200