

CONDUCTOR			BOLT SIZE	CATALOG NO.	FIG. NO.	DIMENSIONS							INSTALLATION TOOLING (# CRIMPS)							WIRE STRIP LENGTH				
FLEX	CODE (AWG)	NAVY				B	C	H	K	L	N	O.D.	T REF.	Z MIN.	DIE INDEX	COLOR CODE	MECHANICAL RATCHET				HYDRAULIC			DIELESS (# CRIMPS)
#6 WELD 61/24	#6 AWG	30												MD7-34R	OUR840	Y2MR	Y750 Y35 Y39	Y46	Y45					
			#10	YAG6CL-TC10-LD	1	.50 [13]	.48 [12]	.78 [20]	.21 [5]	1.30 [33]	.25 [6]	.31 [8]	.08 [2]	.27 [7]	7 OR 374	BLUE	W5CRT X5CRT W5CVT (1)	X5CRT W5CVT (1)	(1 CRIMP)	USCRT (1)	USCRT (1)	USCRT (1)		1/2"
				YAG6CL-TC10-LD-45	2		.78 [20]			1.26 [32]														
				YAG6CL-TC10-LD-90	3		.90 [23]			.76 [19]														
			1/4	YAG6CL-TC14-LD	1		.48 [12]	.78 [20]	.27 [7]	1.43 [36]	.31 [8]	.08 [2]	.33 [8]											
				YAG6CL-TC14-LD-45	2		.90 [23]			1.39 [35]														
				YAG6CL-TC14-LD-90	3		.88 [22]			.88 [22]														
			5/16	YAG6CL-TC516-LD	1		.52 [13]	.78 [20]	.33 [8]	1.49 [38]	.34 [9]	.07 [2]	.36 [9]											
				YAG6CL-TC516-LD-45	2		.89 [23]			1.44 [37]														
				YAG6CL-TC516-LD-90	3		.94 [24]			.94 [24]														
			3/8	YAG6CL-TC38-LD	1		.58 [15]	.77 [20]	.40 [10]	1.61 [41]	.41 [10]	.06 [2]	.42 [11]											
				YAG6CL-TC38-LD-45	2		.87 [22]			1.54 [39]														
				YAG6CL-TC38-LD-90	3		.87 [22]			1.06 [27]														
			1/2	YAG6CL-TC12-LD	1		.75 [19]	.80 [20]	.53 [13]	1.86 [47]	.53 [13]	.12 [3]	.55 [14]	7 OR 374	BLUE	W5CRT X5CRT W5CVT (1)	X5CRT W5CVT (1)	(1 CRIMP)	USCRT (1)	USCRT (1)	USCRT (1)	MECHANICAL: MY29-11 (1) HYDRAULIC: Y644M (1)	1/2"	
				YAG6CL-TC12-LD-45	2		.98 [25]			1.92 [49]														
				YAG6CL-TC12-LD-90	3		.98 [25]			1.34 [34]														

SEE SHEET 1 OF 18 FOR NOTES

HYLUG™	
CAT NO: YAG6CL-TC-LD-	SCALE: FULL SIZE
DRWN: D FILLION 12-17-92	CHECKED: KAY HENRY 12-18-92
ESGN APPVL: C PALANI 6 HESKEY 12-22-92	MFG APPVL: N/A
D.A. APPVL: A LLOYD 12-31-92	MKTG APPVL: T NELSON 01-12-93
CAD FILE: SE208132-SHT03	PH REF: N/A
MOL REF: N/A	PROJECT: DO 52410
BURNDY	
DRAWING NO. SE208132	
SHEET 3 OF 18	

REV.	DATE	DESCRIPTION	BY	C.K'D.
2	10/10/97	CHANGED "H" & "L" DIMS PER FCN (3281).	KRB	JW
1	4/25/96	"H" WAS .78 AND "L" WAS 1.44 FOR 516-45 SIZE PER FCN (2611).	JWA	JLM

REV. 061995