




BOOSTER INFORMATION							
BOOSTER COLOR FOR INSTALLATION	STANDARD PACK QTY.	BOOSTER CATALOG #	MAIN BODY	MATCHING INSTALL FRAME	COMPONENT COLOR INSTALLED	REMOVAL CLIP CATALOG #	BOOSTER COLOR FOR REMOVAL
RED	25	WPBRNBOX25	WTB OR WTBNHS	WTHRBIS	RED	WTOCBR	RED
BLUE	25	WPBBNBOX25	WTB OR WTBNHS	WTHRBIS	BLUE	WTOCBR	RED
YELLOW	25	WPBYNBOX25	WTB OR WTBNHS	WTHYIS	YELLOW	WTOCY	BLUE
MATCHING WEJTAP CONNECTOR SERIES							
BOOSTER COLOR	CONNECTOR CATALOG #	CONDUCTOR RANGE RUN	CONDUCTOR RANGE TAP	MATCHING INSTALL FRAME	CONNECTOR COLOR INSTALLED	REMOVAL CLIP CATALOG #	BOOSTER COLOR FOR REMOVAL
RED	WCR29-WCR37	8 - 1/0	8 - 2	WTHRBIS	RED	WTOCBR	RED
BLUE	WCB10-WCB47	2 - 300	6 - 300	WTHRBIS	BLUE	WTOCBR	RED
YELLOW	WCY48-WCY145	266.8 - 1590	6 - 1590	WTHYIS	YELLOW	WTOCY	BLUE
MATCHING WEJTAP STIRRUP SERIES							
BOOSTER COLOR	STIRRUP CATALOG #	CONDUCTOR RANGE RUN	TIN PLATED COPPER BAIL RANGE	MATCHING INSTALL FRAME	STIRRUP COLOR INSTALLED	REMOVAL CLIP CATALOG #	BOOSTER COLOR FOR REMOVAL
RED	WSSI-WSS2	2 - 6	2	WTHRBIS	RED	WTOCBR	RED
BLUE	WSSMI-WSSM11	1 - 336.4	2 - 4/0	WTHRBIS	BLUE	WTOCBR	RED
YELLOW	WSLI-WSL14	336.4 - 1033.5	1/0 - 4/0	WTHYIS	YELLOW	WTOCY	BLUE
MATCHING WEJTAP POWER LUG SERIES							
BOOSTER COLOR	POWER LUG CATALOG #	CONDUCTOR RANGE RUN	PAD CONFIGURATION	MATCHING INSTALL FRAME	POWER LUG COLOR INSTALLED	REMOVAL CLIP CATALOG #	BOOSTER COLOR FOR REMOVAL
RED			N/A				
BLUE	WCAB30R-WCBB30R	6 STR. - 300	2 OR 4 HOLE PAD	WTHRBIS	BLUE	WTOCBR	RED
YELLOW	WCAY39R-WCAY49R	266.8 - 1113	2 OR 4 HOLE PAD	WTHYIS	YELLOW	WTOCY	BLUE

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	3/30/2010 11:34:00 AM	NEW DRAWING	20749	TRF	LB



BOOSTER ASSEMBLY

THE BURNDY WEJTAP® BOOSTER IS DESIGNED TO PROVIDE RELIABLE AND SAFE PERFORMANCE IN ALL WEATHER CONDITIONS AND IS A KEY COMPONENT IN THE BURNDY WEJTAP® SYSTEM. PRECISION COMPONENTS MOLDED TO TIGHT TOLERANCES MAKE IT IMPERVIOUS TO PROLONGED DAMP OR TEMPORARY SUBMERGED CONDITIONS. MISFIRES ARE ALMOST NON-EXISTENT. BOOSTER IS FITTED WITH A RIM FIRE CARTRIDGE MANUFACTURED FOR BURNDY BY WINCHESTER® AND LOCATED IN A RECESSED CAVITY REDUCING THE POTENTIAL FOR ACCIDENTAL ACTIVATION. THE BURNDY BOOSTER IS DESIGNED SPECIFICALLY FOR THE BURNDY BREECH LOADED WEJTAP® TOOL. AN MSDS SHEET FOR THE CARTRIDGE IS AVAILABLE UPON REQUEST.



REV: PE0200

TO ORDER BURNDY® PRODUCTS CALL		BOOSTER, WEJTAP	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE	
CANADA: 1-800-361-6975 (QUEBEC)		CAT. NO: SEE TABLE	
1-800-387-6487 (ALL OTHER PROVINCES)		DRAWN BY: T. FAUCHER 03/30/2010	
FOR PRODUCT INFO: http://www.burndy.com		CHECKER: L. BROWN 03/30/2010	
		DSN APPVL: L. BROWN 04/07/2010	
		MFG APPVL: S. GONYAW 04/20/2010	
		QA APPVL: --	
		MKT APPVL: S. MOIST 04/20/2010	
		SCALE: N/A	
		PROD FAM: TOOLS, WEJTAP	
		DRAWING NO	
		PROJECT #: --	
		SIZE	
		DOCUMENT TYPE: Sales	
		B	
		REL LEVEL: Released	
		30000180	
		SHEET 1 OF 1	
		A	

