




CATALOG NUMBER	ITEM NUMBER	CABLE OR WIRE SIZE	Ø'A'	Ø'B'	L	SOCKET AND NUT ASSEMBLY
Z2528	220268	1/0 STR. (.373) 2/0 STR CMPCT (.376)	.71 [18]	.61 [15]	.79 [20]	Z28NR
Z2729	220093	3/0 STR (.470) 4/0 STR CMPCT (.475)	.78 [20]	.66 [17]	.91 [23]	Z29NR
Z2929	220387	250 Kcmil (.575) 300 Kcmil CMPCT (.570)	.78 [20]	.66 [17]	.91 [23]	Z29NR
Z3434	220478	500 Kcmil (.814) 600 Kcmil CMPCT (.813)	1.08 [27]	.91 [23]	1.26 [32]	Z34NR
Z4444	220548	1000 Kcmil (1.152)	1.50 [38]	1.27 [32]	1.75 [44]	Z44NR
Z4848	220053	2000 Kcmil (1.631)	2.12 [54]	1.77 [45]	2.50 [64]	---

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	11/09/2016	UPDATED AS PER MARKUP	45273	JR	MB



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- MATERIAL : TUBING BRASS.
- FINISH : TIN PLATED.

TO ORDER BURNDY® PRODUCTS CALL		SPLIT CONE			
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: SEE TABLE			
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: SEE TABLE			
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: PALANI M	11/23/2012		
		CHECKER: W ZAHLMAN	11/27/2012		
		DSN APRVL: W ZAHLMAN	07/02/2013		
		MFG APRVL: K.BRIAN	11/02/2015		
		QA APRVL: K.CHERYL	10/24/2015		
		MKT APRVL:			
		PROD FAM: --		DRAWING NO	REV
		PROJECT #: --	SIZE	50015027	C
		DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
		REL LEVEL: Released			