



CATALOG NUMBER	THREAD SIZE	'B' LENGHT (Inches)
25X50HEBBOX	1/4-20	1/2 [M13]
25X62HEBBOX	1/4-20	5/8 [M16]
25X75HEBBOX	1/4-20	3/4 [M19]
31X100HEBBOX	5/16-18	1 [M24]
31X125HEBBOX	5/16-18	1-1/4 [M30]
31X150HEBBOX	5/16-18	1-1/2 [M36]
31X175HEBBOX	5/16-18	1-3/4 [M42]
31X200HEBBOX	5/16-18	2 [M48]
31X250HEBBOX	5/16-18	2-1/2 [M64]
31X300HEBBOX	5/16-18	3 [M76]
31X50HEBBOX	5/16-18	1/2 [M13]
31X62HEBBOX	5/16-18	5/8 [M16]
31X75HEBBOX	5/16-18	5/8 [M16]
38X325HEBBOX	3/8-16	3-1/4 [M80]
38X350HEBBOX	3/8-16	3-1/2 [M90]
38X400HEBBOX	3/8-16	4 [M100]
38X450HEBBOX	3/8-16	4-1/2 [M114]
38X500HEBBOX	3/8-16	5 [M127]
38X50HEBBOX	3/8-16	1/2 [M13]
38X62HEBBOX	3/8-16	5/8 [M16]
38X75HEBBOX	3/8-16	3/4 [M19]
38X88HEBBOX	3/8-16	7/8 [M22]
44X150HEBBOX	7/16-14	1-1/2 [M39]
44X200HEBBOX	7/16-14	2 [M48]
50X400HABBOX	1/2-13	4 [M100]
50X500HABBOX	1/2-13	5 [M127]
50X75HEBBOX	1/2-13	3/4 [M19]
62X100HEBBOX	5/8-11	1 [M24]
62X125HEBBOX	5/8-11	1-1/4 [M30]
62X150HEBBOX	5/8-11	1-1/2 [M39]
62X175HEBBOX	5/8-11	1-3/4 [M42]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	04/08/2014	DRAWING RELEASED	35732	MVP	MB



NOTES:

1. MATERIAL : SILICON BRONZE
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com		BOLT, SILICON BRONZE, HEX HEAD	
		ITEM NO: N/A	CAT. NO: SEE TABLE
DRAWN BY: MANIMEKALA 04/08/2014		CHECKER: MANIKANDAN B 04/09/2014	
DSN APRVL: G RUGGIERO 07/26/2016		MFG APRVL: --	
QA APRVL: J BRODEUR 07/19/2016		MKT APRVL: K BOUTIN 07/20/2016	
PROD FAM: --	DRAWING NO	REV	
PROJECT #: --	SIZE	50041361	A
DOCUMENT TYPE: SALES	B	SHEET 1 OF 1	
REL LEVEL: Released			